We connect and protect

Basic PDU, EB0403, 400 VAC, 3-PH, 16 A

Data Solutions

CATALOG NUMBER

EB0403

Modular, compact PDU. Ultra-Low Profile Design

FEATURES

Enlogic Basic Power Distribution Units enable power in Cabinets as well as Open Frame Racks and Wall-Mount enclosures
Input Voltage 400 VAC, 3-phase
C13 and C19 outlets
1RU aluminum profile
Adjustable Toolless Mounting

PRODUCT ATTRIBUTES

Product Family: Enlogic
Type: Basic PDU
Product Type: Socket Strip
Socket Type: (36) C13; (6) C19
Socket Quantity: 42
Color: Black
Circuit Breaker: No Circuit Breaker
Switched Outlets: No
Circuit Breaker Quantity: 0
Power Rating: 11.0 kVA
Input Cable Length: 3m
Input Cable Location: Top Feed

Input Voltage: 380 – 415V

Phase: 3 PH

Nominal Voltage: 415V

Max Power Input: 11.0 kVA

On/Off Switch Included: No

Amperage (Derated Amperage): 16 A

Output Voltage: 230VAC

Rack Units: 0U

Plug Type: IEC 60309 516P6 (IP44)

Metering Type: None

Removable Input Cable: No

Material: Steel

Finish: Powder Coated

Height: 1490mm

Width: 52mm

Depth: 53mm

Weight: 6.11kg

Package Quantity: 1

ADDITIONAL PRODUCT DETAILS

Please order bracket for vertical mounting separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.