

# LHX+ Control Unit



The Control Unit enriches the LHX+. It connects to the LHX+ sensors and the motorized coolant valve 23130-607. This enables the cooler to control the coolant air flow based on a chilled (supply) air temperature setpoint. It provides advanced remote monitoring functionality and various setup features.

## FEATURES

Coolant flow control based on chilled (supply) air temperature setpoint. More control features with water control package

Separate, compact 19" control unit without loose wires in upper cabinet section

Clearly marked plug & play sensor connections

## SPECIFICATIONS

- Rack Height:** 2U
- Product Type:** Control Unit
- Material:** Steel

Table 1/2

| Catalog Number | Height | Depth | Works With               | Package Quantity | Color      | Color Code |
|----------------|--------|-------|--------------------------|------------------|------------|------------|
| 23130-668      | 88mm   | 220mm | Varistar,<br>Varistar CP | 1                | Black Grey | RAL 7021   |
| 23130-664      | 88mm   | 220mm | Varistar,<br>Varistar CP | 1                | Black Grey | RAL 7021   |

Table 2/2

| Catalog Number | Finish               | Input Voltage AC | Width   |
|----------------|----------------------|------------------|---------|
| 23130-668      | Aluminum-Zinc Plated | 230V             | 439.5mm |
| 23130-664      | Aluminum-Zinc Plated | 100 – 260V       | 439.5mm |

## ADDITIONAL PRODUCT DETAILS

---

Optional external display.

## WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**