


# Handle Without Spring Loading



IEA handle plunger style or lever style kits.

## CERTIFICATIONS



## FEATURES

Innovative insertion/extraction mechanics

In accordance with PICMG 3.0 R2.0

For stainless steel and aluminium front panels

Ergonomic design

Secure locking

AdvancedTCA IEA plunger or lever style handle

Without spring loading

## SPECIFICATIONS

**Product Type:** Handle

**Material:** Steel

Table 1/1

Catalog Number	Type	Package Quantity	Handle Type
20818-121	Top	10	Plunger
20818-124	Bottom	10	Lever
20818-122	Bottom	10	Plunger
20818-123	Top	10	Lever

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**