

# LED Lights for Cabinets



The enclosure light provides a compact and flexible solution, and offers fast, easy assembly and installation. For mounting flexibility, the LED light can be fastened to the enclosure with screws or quickly attached to any flat steel surfaces with optional magnetic kits. A motion sensor is also available.

## CERTIFICATIONS



## FEATURES

Power cable for LED light mounting into cabinet

Lights can be easily mounted vertically or horizontally

Simple through-wiring based on a plug-and-play system

## SPECIFICATIONS

**Product Type:** Light

Table 1/2

| Catalog Number | Accessory Type | Protection Rating | Package Quantity | Color | Finish       | Type                          |
|----------------|----------------|-------------------|------------------|-------|--------------|-------------------------------|
| 57274          | Lights         | IP20              | 1                | Black | Smooth Matte | Cabinet Light, Terminal Block |
| 57275          | Lights         | IP20              | 2                |       | Smooth Matte | Cabinet Light, Magnet         |
| 60130-114      | Lights         | IP20              | 1                |       | Smooth       | Connection Cable              |
| 57265          | Lights         | IP20              | 1                | Black | Smooth Matte | Cabinet Light                 |
| 57272          | Lights         | IP20              | 1                | Black | Smooth       | Connection Cable              |

| Catalog Number | Accessory Type | Protection Rating | Package Quantity | Color | Finish | Type             |
|----------------|----------------|-------------------|------------------|-------|--------|------------------|
| 57273          | Lights         | IP20              | 1                | Black | Smooth | Connection Cable |

Table 2/2

| Catalog Number | Connection Type               | Light Output | Rated Current | Weight  | Certifications |
|----------------|-------------------------------|--------------|---------------|---------|----------------|
| 57274          | Infeed, Trough-Wiring, 2-Pole |              | 16A           | 0.07kg  | RoHS           |
| 57275          |                               |              |               | 0.08kg  | RoHS           |
| 60130-114      | Infeed, Trough-Wiring, 2-Pole |              | 10A           | 0.083kg | RoHS, EAC      |
| 57265          | Infeed, Trough-Wiring, 2-Pole | 550lm        |               | 0.24kg  | CE, RoHS       |
| 57272          | Infeed, Trough-Wiring, 2-Pole |              | 10A           | 0.3kg   | RoHS           |
| 57273          | Infeed, Trough-Wiring, 2-Pole |              | 10A           | 0.3kg   | RoHS           |

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**