


DIN Rail

Data Solutions

A DIN rail is a standard metal rail widely used for mounting circuit breakers and industrial control equipment inside equipment racks.



FEATURES

Pre-Cut Lengths and with Perforations

Steel with electrogalvanized finishing

Comply with: EN 60715 Standards

SPECIFICATIONS

Product Type: DIN Rail

Table 1/2

| Catalog Number | Material | Height | Length | Finish | Package Quantity | Depth |
|----------------|----------|--------|--------|-------------|------------------|-------|
| 20118-879 | Steel | 35mm | 175mm | Zinc Plated | 4 | 7.5mm |
| 20118-874 | Steel | 35mm | 275mm | Zinc Plated | 4 | 15mm |
| 20118-872 | Steel | 35mm | 125mm | Zinc Plated | 4 | 15mm |
| 20118-883 | Steel | 35mm | 575mm | Zinc Plated | 4 | 7.5mm |
| 20118-875 | Steel | 35mm | 375mm | Zinc Plated | 4 | 15mm |
| 20118-878 | Steel | 35mm | 125mm | Zinc Plated | 4 | 7.5mm |
| 20118-880 | Steel | 35mm | 275mm | Zinc Plated | 4 | 7.5mm |
| 20118-877 | Steel | 35mm | 575mm | Zinc Plated | 4 | 15mm |
| 20118-882 | Steel | 35mm | 475mm | Zinc Plated | 4 | 7.5mm |

| CatalogNumber | Material | Height | Length | Finish | Package Quantity | Depth |
|---------------|----------|--------|--------|-------------|------------------|-------|
| 20118-873 | Steel | 35mm | 175mm | Zinc Plated | 4 | 15mm |
| 20118-881 | Steel | 35mm | 375mm | Zinc Plated | 4 | 7.5mm |
| 20118-876 | Steel | 35mm | 475mm | Zinc Plated | 4 | 15mm |
| 20118-893 | Steel | 35mm | 375mm | Zinc Plated | 10 | 7.5mm |
| 20118-892 | Steel | 35mm | 275mm | Zinc Plated | 10 | 7.5mm |
| 20118-891 | Steel | 35mm | 175mm | Zinc Plated | 10 | 7.5mm |
| 20118-890 | Steel | 35mm | 125mm | Zinc Plated | 10 | 7.5mm |
| 20118-895 | Steel | 35mm | 575mm | Zinc Plated | 10 | 7.5mm |
| 20118-894 | Steel | 35mm | 475mm | Zinc Plated | 10 | 7.5mm |
| 20118-889 | Steel | 35mm | 575mm | Zinc Plated | 10 | 15mm |
| 20118-887 | Steel | 35mm | 375mm | Zinc Plated | 10 | 15mm |
| 20118-885 | Steel | 35mm | 175mm | Zinc Plated | 10 | 15mm |
| 20118-886 | Steel | 35mm | 275mm | Zinc Plated | 10 | 15mm |
| 20118-884 | Steel | 35mm | 125mm | Zinc Plated | 10 | 15mm |
| 20118-888 | Steel | 35mm | 475mm | Zinc Plated | 10 | 15mm |

Table 2/2

| Catalog Number | Width |
|----------------|-------|
| 20118-879 | 175mm |
| 20118-874 | 275mm |
| 20118-872 | 125mm |
| 20118-883 | 575mm |
| 20118-875 | 375mm |
| 20118-878 | 125mm |
| 20118-880 | 275mm |
| 20118-877 | 575mm |
| 20118-882 | 475mm |
| 20118-873 | 175mm |
| 20118-881 | 375mm |
| 20118-876 | 475mm |
| 20118-893 | 375mm |
| 20118-892 | 275mm |
| 20118-891 | 175mm |
| 20118-890 | 125mm |
| 20118-895 | 575mm |

| Catalog Number | Width |
|----------------|-------|
| 20118-894 | 475mm |
| 20118-889 | 575mm |
| 20118-887 | 375mm |
| 20118-885 | 175mm |
| 20118-886 | 275mm |
| 20118-884 | 125mm |
| 20118-888 | 475mm |

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE