We connect and protect

Outdoor Modular 29 U 1530H 2100W 800D

Data Solutions

CATALOG NUMBER

10149-659

Telecom and Railway applications require sophisticated electronics in outdoor setups. nVent SCHROFF Outdoor cabinets shield such electronic components from extreme weather and vandalism, ensuring operational continuity. Modular contruction allows multiple configurations in size and function along with multiple cooling options.

FEATURES

- Aluminium profile frame with removable, double-walled cladding
- IP 55 or NEMA 12~
- Double-walled
- Extensive range of 19" cabinet accessories
- Access to cabinet from front, all sides possible upon request
- 100 mm high plinth, 200 and 300 mm possible
- Top cover with louvers, can be upgraded with fans or A/C unit
- RAL 7035 powder coating, other colors available upon request

PRODUCT ATTRIBUTES

- Product Type: Outdoor Cabinet
- Product Family: Modular
- Rack Height: 29U
- Height: 1530mm
- Width: 2100mm
- Depth: 800mm
- Wall Type: Double Walled

Door Type: Plain; Triple Door
Burglar Resistance: Optional
Cooling: Passive
EMC Shielding: Optional
Frame Material: Aluminum
Battery Compartment: Optional
Finish: Powder Coated
Material: Aluminum; Steel
Mounting Setup: Optional
Package Quantity: 1
Plinth Height: 100mm

ADDITIONAL PRODUCT DETAILS

Height dimensions are without base/plinth.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.