We connect and protect

# Varistar CP Steel Door, Perforated With 1-Point Locking, Key Plate Only, RAL 7021, 33 U, 1600H 600W

## Data Solutions

### CATALOG NUMBER

**21630-511**

Varistar CP Perforated Steel Door, IP 20 with Single Point Locking.

### FEATURES

- Perforated steel door with single point locking for IP 20 protection class
- Opening angle 180°
- Key lock cover

### PRODUCT ATTRIBUTES

- Rack Height: 33U
- Height: 1600mm
- Width: 600mm
- Locking Type: Single Point Locking
- Package Quantity: 1
- Color: Black Grey
- Color Code: RAL 7021
- Complies With: IEC 61587-1
- Material: Steel

Product Family: Varistar CP

Product Type: Cabinet Door

Protection Rating: IP20

Type: Steel Door, Perforated

Works With: Varistar CP

Net Weight: 12.03kg

## ADDITIONAL PRODUCT DETAILS

24U - 33U IP20 doors have 2 hinges, 38U - 52U IP20 doors have 3 hinges to ensure robust IP20 closing structures for taller cabinets

Please order lever handle 24630003 and the DIN lock separately if you want to replace the 1333 DIN lock lever handle

Please purchase the grounding kit separately.

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.