

Varistar CP Mobile Frame



Varistar welded steel frame for static load requirements. For 19", ETSI or mounting plate integration. For mobile applications.

FEATURES

Welded, finish powder-coated, black gray, RAL 7021

SPECIFICATIONS

- Dynamic Load:** 1000kg
- Static Load:** 1600kg
- Product Type:** Cabinet/Rack Frame
- Material:** Steel

Table 1/4

| Catalog Number | Rack Height | Height | Width | Depth | Package Quantity | Color |
|----------------|-------------|--------|-------|--------|------------------|------------|
| 20630-215 | 33U | 1600mm | 800mm | 600mm | 1 | Black Grey |
| 20630-211 | 33U | 1600mm | 600mm | 600mm | 1 | Black Grey |
| 20630-231 | 42U | 2000mm | 600mm | 1100mm | 1 | Black Grey |
| 20630-217 | 33U | 1600mm | 800mm | 900mm | 1 | Black Grey |
| 20630-214 | 33U | 1600mm | 600mm | 1000mm | 1 | Black Grey |
| 20630-212 | 33U | 1600mm | 600mm | 800mm | 1 | Black Grey |
| 20630-213 | 33U | 1600mm | 600mm | 900mm | 1 | Black Grey |
| 20630-232 | 42U | 2000mm | 600mm | 1200mm | 1 | Black Grey |
| 20630-210 | 29U | 1400mm | 800mm | 1000mm | 1 | Black Grey |
| 20630-218 | 33U | 1600mm | 800mm | 1000mm | 1 | Black Grey |
| 20630-209 | 29U | 1400mm | 800mm | 900mm | 1 | Black Grey |

| Catalog Number | Rack Height | Height | Width | Depth | Package Quantity | Color |
|----------------|-------------|--------|-------|--------|------------------|------------|
| 20630-206 | 29U | 1400mm | 600mm | 1000mm | 1 | Black Grey |
| 20630-205 | 29U | 1400mm | 600mm | 900mm | 1 | Black Grey |
| 20630-237 | 42U | 2000mm | 800mm | 1100mm | 1 | Black Grey |
| 20630-216 | 33U | 1600mm | 800mm | 800mm | 1 | Black Grey |
| 20630-199 | 24U | 1200mm | 800mm | 600mm | 1 | Black Grey |
| 20630-202 | 24U | 1200mm | 800mm | 1000mm | 1 | Black Grey |
| 20630-201 | 24U | 1200mm | 800mm | 900mm | 1 | Black Grey |
| 20630-200 | 24U | 1200mm | 800mm | 800mm | 1 | Black Grey |
| 20630-221 | 38U | 1800mm | 600mm | 900mm | 1 | Black Grey |

Table 2/4

| Catalog Number | Rack Height | Height | Width | Depth | Package Quantity | Color |
|----------------|-------------|--------|-------|--------|------------------|------------|
| 20630-208 | 29U | 1400mm | 800mm | 800mm | 1 | Black Grey |
| 20630-222 | 38U | 1800mm | 600mm | 1000mm | 1 | Black Grey |
| 20630-225 | 38U | 1800mm | 800mm | 900mm | 1 | Black Grey |
| 20630-207 | 29U | 1400mm | 800mm | 600mm | 1 | Black Grey |
| 20630-255 | 52U | 2450mm | 800mm | 1100mm | 1 | Black Grey |
| 20630-226 | 38U | 1800mm | 800mm | 1000mm | 1 | Black Grey |
| 20630-251 | 52U | 2450mm | 600mm | 1000mm | 1 | Black Grey |
| 20630-254 | 52U | 2450mm | 800mm | 1000mm | 1 | Black Grey |
| 20630-204 | 29U | 1400mm | 600mm | 800mm | 1 | Black Grey |
| 20630-252 | 52U | 2450mm | 600mm | 1100mm | 1 | Black Grey |
| 20630-253 | 52U | 2450mm | 600mm | 1200mm | 1 | Black Grey |
| 20630-256 | 52U | 2450mm | 800mm | 1200mm | 1 | Black Grey |
| 20630-203 | 29U | 1400mm | 600mm | 600mm | 1 | Black Grey |
| 20630-236 | 42U | 2000mm | 800mm | 1000mm | 1 | Black Grey |
| 20630-224 | 38U | 1800mm | 800mm | 800mm | 1 | Black Grey |
| 20630-242 | 47U | 2200mm | 600mm | 1000mm | 1 | Black Grey |
| 20630-241 | 47U | 2200mm | 600mm | 900mm | 1 | Black Grey |
| 20630-227 | 42U | 2000mm | 600mm | 600mm | 1 | Black Grey |
| 20630-240 | 47U | 2200mm | 600mm | 800mm | 1 | Black Grey |
| 20630-249 | 47U | 2200mm | 800mm | 1100mm | 1 | Black Grey |

Table 3/4

| Catalog Number | Rack Height | Height | Width | Depth | Package Quantity | Color |
|----------------|-------------|--------|-------|--------|------------------|------------|
| 20630-239 | 47U | 2200mm | 600mm | 600mm | 1 | Black Grey |
| 20630-228 | 42U | 2000mm | 600mm | 800mm | 1 | Black Grey |
| 20630-244 | 47U | 2200mm | 600mm | 1200mm | 1 | Black Grey |
| 20630-235 | 42U | 2000mm | 800mm | 900mm | 1 | Black Grey |
| 20630-250 | 47U | 2200mm | 800mm | 1200mm | 1 | Black Grey |
| 20630-229 | 42U | 2000mm | 600mm | 900mm | 1 | Black Grey |
| 20630-193 | 24U | 1200mm | 600mm | 600mm | 1 | Black Grey |
| 20630-234 | 42U | 2000mm | 800mm | 800mm | 1 | Black Grey |
| 20630-233 | 42U | 2000mm | 800mm | 600mm | 1 | Black Grey |
| 20630-230 | 42U | 2000mm | 600mm | 1000mm | 1 | Black Grey |
| 20630-245 | 47U | 2200mm | 800mm | 600mm | 1 | Black Grey |
| 20630-246 | 47U | 2200mm | 800mm | 800mm | 1 | Black Grey |
| 20630-194 | 24U | 1200mm | 600mm | 800mm | 1 | Black Grey |
| 20630-247 | 47U | 2200mm | 800mm | 900mm | 1 | Black Grey |
| 20630-223 | 38U | 1800mm | 800mm | 600mm | 1 | Black Grey |
| 20630-248 | 47U | 2200mm | 800mm | 1000mm | 1 | Black Grey |
| 20630-243 | 47U | 2200mm | 600mm | 1100mm | 1 | Black Grey |
| 20630-195 | 24U | 1200mm | 600mm | 900mm | 1 | Black Grey |
| 20630-220 | 38U | 1800mm | 600mm | 800mm | 1 | Black Grey |
| 20630-219 | 38U | 1800mm | 600mm | 600mm | 1 | Black Grey |

Table 4/4

| Catalog Number | Rack Height | Height | Width | Depth | Package Quantity | Color |
|----------------|-------------|--------|-------|--------|------------------|------------|
| 20630-196 | 24U | 1200mm | 600mm | 1000mm | 1 | Black Grey |
| 20630-238 | 42U | 2000mm | 800mm | 1200mm | 1 | Black Grey |

Table 1/4

| Catalog Number | Color Code | Complies With | Frame Material | Type | Works With |
|----------------|------------|--------------------------|----------------|--------|-------------|
| 20630-215 | RAL 7021 | IEC 61587-1, IEC 61587-3 | Steel | Mobile | Varistar CP |
| 20630-211 | RAL 7021 | IEC 61587-1, IEC 61587-3 | Steel | Mobile | Varistar CP |
| 20630-231 | RAL 7021 | IEC 61587-1, IEC 61587-3 | Steel | Mobile | Varistar CP |

| Catalog Number | Color Code | Complies With | Frame Material | Type | Works With |
|----------------|------------|--------------------------|----------------|--------|-------------|
| 20630-217 | RAL 7021 | IEC 61587-1, IEC 61587-3 | Steel | Mobile | Varistar CP |
| 20630-214 | RAL 7021 | IEC 61587-1, IEC 61587-3 | Steel | Mobile | Varistar CP |
| 20630-212 | RAL 7021 | IEC 61587-1, IEC 61587-3 | Steel | Mobile | Varistar CP |
| 20630-213 | RAL 7021 | IEC 61587-1, IEC 61587-3 | Steel | Mobile | Varistar CP |
| 20630-232 | RAL 7021 | IEC 61587-1, IEC 61587-3 | Steel | Mobile | Varistar CP |
| 20630-210 | RAL 7021 | IEC 61587-1, IEC 61587-3 | Steel | Mobile | Varistar CP |
| 20630-218 | RAL 7021 | IEC 61587-1, IEC 61587-3 | Steel | Mobile | Varistar CP |
| 20630-209 | RAL 7021 | IEC 61587-1, IEC 61587-3 | Steel | Mobile | Varistar CP |
| 20630-206 | RAL 7021 | IEC 61587-1, IEC 61587-3 | Steel | Mobile | Varistar CP |
| 20630-205 | RAL 7021 | IEC 61587-1, IEC 61587-3 | Steel | Mobile | Varistar CP |
| 20630-237 | RAL 7021 | IEC 61587-1, IEC 61587-3 | Steel | Mobile | Varistar CP |
| 20630-216 | RAL 7021 | IEC 61587-1, IEC 61587-3 | Steel | Mobile | Varistar CP |
| 20630-199 | RAL 7021 | IEC 61587-1, IEC 61587-3 | Steel | Mobile | Varistar CP |
| 20630-202 | RAL 7021 | IEC 61587-1, IEC 61587-3 | Steel | Mobile | Varistar CP |
| 20630-201 | RAL 7021 | IEC 61587-1, IEC 61587-3 | Steel | Mobile | Varistar CP |
| 20630-200 | RAL 7021 | IEC 61587-1, IEC 61587-3 | Steel | Mobile | Varistar CP |
| 20630-221 | RAL 7021 | IEC 61587-1, IEC 61587-3 | Steel | Mobile | Varistar CP |

Table 2/4

| Catalog Number | Color Code | Complies With | Frame Material | Type | Works With |
|----------------|------------|--------------------------|----------------|--------|-------------|
| 20630-208 | RAL 7021 | IEC 61587-1, IEC 61587-3 | Steel | Mobile | Varistar CP |
| 20630-222 | RAL 7021 | IEC 61587-1, IEC 61587-3 | Steel | Mobile | Varistar CP |

| Catalog Number | Color Code | Complies With | Frame Material | Type | Works With |
|----------------|------------|--------------------------|----------------|--------|-------------|
| 20630-225 | RAL 7021 | IEC 61587-1, IEC 61587-3 | Steel | Mobile | Varistar CP |
| 20630-207 | RAL 7021 | IEC 61587-1, IEC 61587-3 | Steel | Mobile | Varistar CP |
| 20630-255 | RAL 7021 | IEC 61587-1, IEC 61587-3 | Steel | Mobile | Varistar CP |
| 20630-226 | RAL 7021 | IEC 61587-1, IEC 61587-3 | Steel | Mobile | Varistar CP |
| 20630-251 | RAL 7021 | IEC 61587-1, IEC 61587-3 | Steel | Mobile | Varistar CP |
| 20630-254 | RAL 7021 | IEC 61587-1, IEC 61587-3 | Steel | Mobile | Varistar CP |
| 20630-204 | RAL 7021 | IEC 61587-1, IEC 61587-3 | Steel | Mobile | Varistar CP |
| 20630-252 | RAL 7021 | IEC 61587-1, IEC 61587-3 | Steel | Mobile | Varistar CP |
| 20630-253 | RAL 7021 | IEC 61587-1, IEC 61587-3 | Steel | Mobile | Varistar CP |
| 20630-256 | RAL 7021 | IEC 61587-1, IEC 61587-3 | Steel | Mobile | Varistar CP |
| 20630-203 | RAL 7021 | IEC 61587-1, IEC 61587-3 | Steel | Mobile | Varistar CP |
| 20630-236 | RAL 7021 | IEC 61587-1, IEC 61587-3 | Steel | Mobile | Varistar CP |
| 20630-224 | RAL 7021 | IEC 61587-1, IEC 61587-3 | Steel | Mobile | Varistar CP |
| 20630-242 | RAL 7021 | IEC 61587-1, IEC 61587-3 | Steel | Mobile | Varistar CP |
| 20630-241 | RAL 7021 | IEC 61587-1, IEC 61587-3 | Steel | Mobile | Varistar CP |
| 20630-227 | RAL 7021 | IEC 61587-1, IEC 61587-3 | Steel | Mobile | Varistar CP |
| 20630-240 | RAL 7021 | IEC 61587-1, IEC 61587-3 | Steel | Mobile | Varistar CP |
| 20630-249 | RAL 7021 | IEC 61587-1, IEC 61587-3 | Steel | Mobile | Varistar CP |

Table 3/4

| Catalog Number | Color Code | Complies With | Frame Material | Type | Works With |
|----------------|------------|--------------------------|----------------|--------|-------------|
| 20630-239 | RAL 7021 | IEC 61587-1, IEC 61587-3 | Steel | Mobile | Varistar CP |

| Catalog Number | Color Code | Complies With | Frame Material | Type | Works With |
|----------------|------------|--------------------------|----------------|--------|-------------|
| 20630-228 | RAL 7021 | IEC 61587-1, IEC 61587-3 | Steel | Mobile | Varistar CP |
| 20630-244 | RAL 7021 | IEC 61587-1, IEC 61587-3 | Steel | Mobile | Varistar CP |
| 20630-235 | RAL 7021 | IEC 61587-1, IEC 61587-3 | Steel | Mobile | Varistar CP |
| 20630-250 | RAL 7021 | IEC 61587-1, IEC 61587-3 | Steel | Mobile | Varistar CP |
| 20630-229 | RAL 7021 | IEC 61587-1, IEC 61587-3 | Steel | Mobile | Varistar CP |
| 20630-193 | RAL 7021 | IEC 61587-1, IEC 61587-3 | Steel | Mobile | Varistar CP |
| 20630-234 | RAL 7021 | IEC 61587-1, IEC 61587-3 | Steel | Mobile | Varistar CP |
| 20630-233 | RAL 7021 | IEC 61587-1, IEC 61587-3 | Steel | Mobile | Varistar CP |
| 20630-230 | RAL 7021 | IEC 61587-1, IEC 61587-3 | Steel | Mobile | Varistar CP |
| 20630-245 | RAL 7021 | IEC 61587-1, IEC 61587-3 | Steel | Mobile | Varistar CP |
| 20630-246 | RAL 7021 | IEC 61587-1, IEC 61587-3 | Steel | Mobile | Varistar CP |
| 20630-194 | RAL 7021 | IEC 61587-1, IEC 61587-3 | Steel | Mobile | Varistar CP |
| 20630-247 | RAL 7021 | IEC 61587-1, IEC 61587-3 | Steel | Mobile | Varistar CP |
| 20630-223 | RAL 7021 | IEC 61587-1, IEC 61587-3 | Steel | Mobile | Varistar CP |
| 20630-248 | RAL 7021 | IEC 61587-1, IEC 61587-3 | Steel | Mobile | Varistar CP |
| 20630-243 | RAL 7021 | IEC 61587-1, IEC 61587-3 | Steel | Mobile | Varistar CP |
| 20630-195 | RAL 7021 | IEC 61587-1, IEC 61587-3 | Steel | Mobile | Varistar CP |
| 20630-220 | RAL 7021 | IEC 61587-1, IEC 61587-3 | Steel | Mobile | Varistar CP |
| 20630-219 | RAL 7021 | IEC 61587-1, IEC 61587-3 | Steel | Mobile | Varistar CP |

Table 4/4

| Catalog Number | Color Code | Complies With | Frame Material | Type | Works With |
|----------------|------------|---------------|----------------|------|------------|
|----------------|------------|---------------|----------------|------|------------|

| | | | | | |
|-----------|----------|--------------------------|-------|--------|-------------|
| 20630-196 | RAL 7021 | IEC 61587-1, IEC 61587-3 | Steel | Mobile | Varistar CP |
| 20630-238 | RAL 7021 | IEC 61587-1, IEC 61587-3 | Steel | Mobile | Varistar CP |

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE