

Varistar CP Server Cabinet



Welded steel frame for high static load requirements.
Prepared for 19" integration of IT assets.

FEATURES

Preconfigured, ready to use cabinet

Static load-carrying capacity up to 1600 kg, dynamic 1000 kg

Ingress protection class IP 20

Installation of different IT equipment possible

Integrated air panels for front to back cooling

Can be easily integrated into aisle containment system

SPECIFICATIONS

Static Load:	1600kg
Product Type:	Rack
Cladding Color Code:	RAL 7021
Frame Material:	Steel

Table 1/2

Catalog Number	Rack Height	Height	Cladding Material	Width	Cladding Color	Depth
10630-019	47U	2200mm	Steel	600mm	Black Grey	1200mm
10630-017	42U	2000mm	Steel	600mm	Black Grey	1200mm
10630-026	47U	2200mm	Steel	800mm	Black Grey	1200mm

Catalog Number	Rack Height	Height	Cladding Material	Width	Cladding Color	Depth
10630-023	42U	2000mm	Steel	600mm	Black Grey	1200mm
10630-018	42U	2000mm	Steel	800mm	Black Grey	1200mm
10630-020	47U	2200mm	Steel	800mm	Black Grey	1200mm
10630-024	42U	2000mm	Steel	800mm	Black Grey	1200mm
10630-025	47U	2200mm	Steel	600mm	Black Grey	1200mm

Table 2/2

Catalog Number	Type	Package Quantity	Dynamic Load	Finish	Material
10630-019	Standard	1	1000kgf	Powder Coated	Steel
10630-017	Standard	1	1000kgf	Powder Coated	Steel
10630-026	Side-by-Side	1	1000kgf	Powder Coated	Steel
10630-023	Side-by-Side	1	1000kgf	Powder Coated	Steel
10630-018	Standard	1	1000kgf	Powder Coated	Steel
10630-020	Standard	1	1000kgf	Powder Coated	Steel
10630-024	Side-by-Side	1	1000kgf	Powder Coated	Steel
10630-025	Side-by-Side	1	1000kgf	Powder Coated	Steel

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE