

Varistar CP Side Panel, Divided, Screw-Fixed



Screw assembly two side panels to close the height of Varistar CP cabinet.

FEATURES

Steel, 1 mm

2 splitted Side panel without grounding kit

SPECIFICATIONS

Product Type: Cabinet/Rack Panel

Protection Rating: IP20

Table 1/2

Catalog Number	Rack Height	Height	Depth	Package Quantity	Color	Color Code
21630-060	52U	2450mm	1200mm	2	Black Grey	RAL 7021
21630-052	42U	2000mm	1000mm	2	Black Grey	RAL 7021
21630-055	47U	2200mm	1000mm	2	Black Grey	RAL 7021
21630-054	42U	2000mm	1200mm	2	Black Grey	RAL 7021
21630-056	47U	2200mm	1100mm	2	Black Grey	RAL 7021
21630-057	47U	2200mm	1200mm	2	Black Grey	RAL 7021
21630-058	52U	2450mm	1000mm	2	Black Grey	RAL 7021
21630-059	52U	2450mm	1100mm	2	Black Grey	RAL 7021
21630-053	42U	2000mm	1100mm	2	Black Grey	RAL 7021

Table 2/2

Catalog Number	Finish	Material	Type
21630-060	Powder Coated	Steel	Side Panel, Screw Fixed

Catalog Number	Finish	Material	Type
21630-052	Powder Coated	Steel	Side Panel, Screw Fixed
21630-055	Powder Coated	Steel	Side Panel, Screw Fixed
21630-054	Powder Coated	Steel	Side Panel, Screw Fixed
21630-056	Powder Coated	Steel	Side Panel, Screw Fixed
21630-057	Powder Coated	Steel	Side Panel, Screw Fixed
21630-058	Powder Coated	Steel	Side Panel, Screw Fixed
21630-059	Powder Coated	Steel	Side Panel, Screw Fixed
21630-053	Powder Coated	Steel	Side Panel, Screw Fixed

ADDITIONAL PRODUCT DETAILS

Please purchase the grounding kit separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE