

nVent CADDY Cat 425 Adjustable Cable Support with Flange Clip, 100 mm, 150 mm dia, 3.2–6.4 mm Flange

Data Solutions

CATALOG NUMBER

CAT42524SM



CERTIFICATIONS



FEATURES

Requires only a hammer to install

Provides optimal support for high-performance data cable, up to and including Cat 5e, Cat 6, Cat 6A, Cat 7 and fibre optic

Simple unlocking and locking of bar allows for additional cables to be added easily after installation

Adjustable strap allows for multiple support sizes to reduce inventory

Cost effective alternative to expensive cable tray


cULus® Listed and complies with NEC® and TIA requirements for structured cabling systems

Suitable for air handling spaces (plenum)

PRODUCT ATTRIBUTES

Article Number: 181620
Material: Steel; Polyethylene; Spring Steel
Finish: nVent CADDY Armour; Electrogalvanized
Diameter (Ø): 100mm; 150mm
Area: 13181mm²
Cable Capacity, Cat 5e: 425
Cable Capacity, Cat 6: 325
Cable Capacity, Cat 6A: 210
Flange Thickness (FT): 3.2 – 6.4mm
Static Load: 450N

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE