

## ProLine Levelers



Four post-type levelers allow adjustment for uneven floors. Levelers can be attached to the bottom of a frame or to a 0-mm solid base. Levelers are plated and the leveler base is capped with black plastic to provide resistance to marring.

### FEATURES

---

Adjustable for 17-mm to 35-mm height Four levelers will support a maximum of 453.6 kg (1000 lbs.)

Ball and socket construction

Four levelers will support a maximum of 453.6 kg (1000 lbs.)

## SPECIFICATIONS

Table 1/1

Catalog Number	Article Number	Material	Finish
PLM12	98140	Mild Steel	Plated

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**