

Single-Sided Solid-Steel Shelf

Data Solutions



The Single-Sided Solid-Steel Shelf mounts to either front or rear flange of open-frame rack, supporting equipment that does not get mounted into rack angles. It uses 3U of rack space and is load rated for 150 lb. (68.0 kg).

FEATURES

The Single-Sided Solid-Steel Shelf mounts to either front or rear flange of open-frame rack, supporting equipment that does not get mounted into rack angles

It uses 3U of rack space and is load rated for 150 lb. (68.0 kg)

SPECIFICATIONS

Table 1/2

| Catalog Number | Article Number | Material | Finish | Color | Color Code | Thickness |
|----------------|----------------|------------|---------------|-----------|------------|-----------|
| ESH19S | 35249 | Mild Steel | Powder Coated | Jet Black | RAL 9005 | 1.52mm |
| ESH23S | 35259 | Mild Steel | Powder Coated | Jet Black | RAL 9005 | 1.52mm |

Table 2/2

| Catalog Number | Article Number | Rack Units | Height | Width | Depth |
|----------------|----------------|------------|--------|-------|-------|
| ESH19S | 35249 | 3U | 123mm | 482mm | 267mm |
| ESH23S | 35259 | 3U | 123mm | 584mm | 267mm |

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE