

Threaded Rod



FEATURES

Cut to length as needed

According to standard DIN 976-1 / ISO 7412

Property Class 4.8

SPECIFICATIONS

Table 1/2

Catalog Number	Article Number	E-Number	Material	Finish	Quality Class	Rod Size (RS)
050M61000S4	592700		Stainless Steel 304 (EN 1.4301)		70	M6
050M61000	592570	1340762	Steel	Electrogalvanized	4.8	M6
050M101000S4	592740	3534926	Stainless Steel 304 (EN 1.4301)		70	M10
050M121000	592630	1340771	Steel	Electrogalvanized	4.8	M12
050M161000	400332	3435866	Steel	Electrogalvanized	4.8	M16
050M101000HD	592615	1319921	Steel	Hot-Dip Galvanized	4.8	M10


CatalogNumber	Article Number	E-Number	Material	Finish	Quality Class	Rod Size (RS)
050M81000S4	592720	3534922	Stainless Steel 304 (EN 1.4301)		70	M8
050M121000HD	592635	3435975	Steel	Hot-Dip Galvanized	4.8	M12
050M81000	592590	1340765	Steel	Electrogalvaniz ed	4.8	M8
050M121000S4	592760	3534931	Stainless Steel 304 (EN 1.4301)		70	M12
050M101000	592610	1340768	Steel	Electrogalvaniz ed	4.8	M10
050M122000	592640	1340773	Steel	Electrogalvaniz ed	4.8	M12
050M82000	592600	1340766	Steel	Electrogalvaniz ed	4.8	M8
050M103000	592670	1340770	Steel	Electrogalvaniz ed	4.8	M10
050M62000	592580	1340763	Steel	Electrogalvaniz ed	4.8	M6
050M63000	592650	1340764	Steel	Electrogalvaniz ed	4.8	M6
050M123000	592680	1340774	Steel	Electrogalvaniz ed	4.8	M12
050M102000	592620	1340769	Steel	Electrogalvaniz ed	4.8	M10
050M83000	592660	1340767	Steel	Electrogalvaniz ed	4.8	M8
050M82000S4	592730	3534924	Stainless Steel 304 (EN 1.4301)		70	M8
050M62000S4	592710		Stainless Steel 304 (EN 1.4301)		70	M6
050M102000S4	592750	3534928	Stainless Steel 304 (EN 1.4301)		70	M10

Table 2/2

Catalog Number	Article Number	E-Number	Length (L)	Static Load
050M61000S4	592700		1000mm	2400N
050M61000	592570	1340762	1000mm	2400N

Catalog Number	Article Number	E-Number	Length (L)	Static Load
050M101000S4	592740	3534926	1000mm	7000N
050M121000	592630	1340771	1000mm	10000N
050M161000	400332	3435866	1000mm	18000N
050M101000HD	592615	1319921	1000mm	7000N
050M81000S4	592720	3534922	1000mm	4500N
050M121000HD	592635	3435975	1000mm	10000N
050M81000	592590	1340765	1000mm	4500N
050M121000S4	592760	3534931	1000mm	10000N
050M101000	592610	1340768	1000mm	7000N
050M122000	592640	1340773	2000mm	10000N
050M82000	592600	1340766	2000mm	4500N
050M103000	592670	1340770	3000mm	7000N
050M62000	592580	1340763	2000mm	2400N
050M63000	592650	1340764	3000mm	2400N
050M123000	592680	1340774	3000mm	10000N
050M102000	592620	1340769	2000mm	7000N
050M83000	592660	1340767	3000mm	4500N
050M82000S4	592730	3534924	2000mm	4500N
050M62000S4	592710		2000mm	2400N
050M102000S4	592750	3534928	2000mm	7000N

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE

