We connect and protect

Door Contact Switch Without Cable

Data Solutions

CATALOG NUMBER

20118-810



Door contact switch with magnetic contact, allows operational efficiency. This product is easy handlable by plug and play.

CERTIFICATIONS

RoHS COMPLIANT

FEATURES

Door contact switch (without connection cable)

PRODUCT ATTRIBUTES

Product Type: Switch
Depth: 33.5mm
Height: 76.5mm
Operating Temperature: –25 to 75°C
Protection Rating: IP66
Width: 31mm
Complies With: UL® 508; EN 50047 form B

Current Rating: 3 – 6A
Gross Weight: 0.1kg
Package Quantity: 1
Voltage: 24 – 230V
Wire Size: 0.5 – 2.5mm²

ADDITIONAL PRODUCT DETAILS

Please order bracket for installation of door switch (Varistar, Novastar, Eurorack) separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.