

Seismic Spring Mount



The Vibration Isolation Mount line from nVent CADDY is used to minimize vibrations produced by supported systems such as mechanical equipment, pumps, ductwork, piping, and in-line, exhaust and cabinet fans.

FEATURES

Used to support HVAC equipment, generators, compressors, pumps, chillers and cooling towers

Used when resistance to wind or seismic forces is required

Powder coated steel housing

Elements are color coded for accurate selection and easy field verification

Steel cups provide uniform loading

Built-in leveling device allows for fine-tuning adjustment

SPECIFICATIONS

Table 1/3

| Catalog Number | Article Number | Length | Width | Height | Ultimate Static Load | Deflection |
|----------------|----------------|---------|---------|----------|----------------------|------------|
| VIBSSM1C1200 | 801632 | 101.6mm | 228.6mm | 203.2mm | 5338N | 25.4mm |
| VIBSSM1B200 | 801615 | 101.6mm | 177.8mm | 187.33mm | 890N | 25.4mm |
| VIBSSM1C1600 | 801634 | 101.6mm | 228.6mm | 203.2mm | 7117N | 25.4mm |
| VIBSSM1B300 | 801616 | 101.6mm | 177.8mm | 187.33mm | 1335N | 25.4mm |
| VIBSSM1C150 | 801626 | 101.6mm | 228.6mm | 203.2mm | 668N | 25.4mm |
| VIBSSM1B050 | 801613 | 101.6mm | 177.8mm | 187.33mm | 223N | 25.4mm |
| VIBSSM1B400 | 801617 | 101.6mm | 177.8mm | 187.33mm | 1780N | 25.4mm |
| VIBSSM1C1400 | 801633 | 101.6mm | 228.6mm | 203.2mm | 6228N | 25.4mm |
| VIBSSM1A200 | 801609 | 76.2mm | 152.4mm | 117.48mm | 890N | 25.4mm |

| Catalog Number | Article Number | Length | Width | Height | Ultimate Static Load | Deflection |
|----------------|----------------|---------|---------|----------|----------------------|------------|
| VIBSSM1B500 | 801618 | 101.6mm | 177.8mm | 187.33mm | 2224N | 25.4mm |
| VIBSSM1A100 | 801608 | 76.2mm | 152.4mm | 117.48mm | 445N | 25.4mm |
| VIBSSM1A500 | 801612 | 76.2mm | 152.4mm | 117.48mm | 2224N | 25.4mm |
| VIBSSM1C1000 | 801631 | 101.6mm | 228.6mm | 203.2mm | 4448N | 25.4mm |
| VIBSSM1B600 | 801619 | 101.6mm | 177.8mm | 187.33mm | 2669N | 25.4mm |
| VIBSSM1A300 | 801610 | 76.2mm | 152.4mm | 117.48mm | 1335N | 25.4mm |
| VIBSSM1B700 | 801620 | 101.6mm | 177.8mm | 187.33mm | 3114N | 25.4mm |
| VIBSSM1B900 | 801622 | 101.6mm | 177.8mm | 187.33mm | 4004N | 25.4mm |
| VIBSSM1A400 | 801611 | 76.2mm | 152.4mm | 117.48mm | 1780N | 25.4mm |
| VIBSSM1B800 | 801621 | 101.6mm | 177.8mm | 187.33mm | 3559N | 25.4mm |
| VIBSSM1A065 | 801607 | 76.2mm | 152.4mm | 117.48mm | 290N | 25.4mm |

Table 2/3

| Catalog Number | Article Number | Length | Width | Height | Ultimate Static Load | Deflection |
|----------------|----------------|---------|---------|----------|----------------------|------------|
| VIBSSM1C400 | 801628 | 101.6mm | 228.6mm | 203.2mm | 1780N | 25.4mm |
| VIBSSM1C600 | 801629 | 101.6mm | 228.6mm | 203.2mm | 2669N | 25.4mm |
| VIBSSM1B1000 | 801623 | 101.6mm | 177.8mm | 187.33mm | 4448N | 25.4mm |
| VIBSSM1B1100 | 801624 | 101.6mm | 177.8mm | 187.33mm | 4893N | 25.4mm |
| VIBSSM1C300 | 801627 | 101.6mm | 228.6mm | 203.2mm | 1335N | 25.4mm |
| VIBSSM1A040 | 801606 | 76.2mm | 152.4mm | 117.48mm | 178N | 25.4mm |
| VIBSSM1C800 | 801630 | 101.6mm | 228.6mm | 203.2mm | 3559N | 25.4mm |
| VIBSSM1B1200 | 801625 | 101.6mm | 177.8mm | 187.33mm | 5338N | 25.4mm |
| VIBSSM1C2000 | 801636 | 101.6mm | 228.6mm | 203.2mm | 8896N | 25.4mm |
| VIBSSM1B100 | 801614 | 101.6mm | 177.8mm | 187.33mm | 445N | 25.4mm |
| VIBSSM1C1800 | 801635 | 101.6mm | 228.6mm | 203.2mm | 8007N | 25.4mm |
| VIBSSM2A1400 | 801649 | 101.6mm | 177.8mm | 193.68mm | 6228N | 50.8mm |
| VIBSSM2B1200 | 801662 | 101.6mm | 228.6mm | 203.2mm | 5338N | 50.8mm |
| VIBSSM2B400 | 801655 | 101.6mm | 228.6mm | 203.2mm | 1780N | 50.8mm |
| VIBSSM2A065 | 801638 | 101.6mm | 177.8mm | 193.68mm | 290N | 50.8mm |
| VIBSSM2B050 | 801651 | 101.6mm | 228.6mm | 203.2mm | 223N | 50.8mm |
| VIBSSM2A600 | 801643 | 101.6mm | 177.8mm | 193.68mm | 2669N | 50.8mm |
| VIBSSM2A1600 | 801650 | 101.6mm | 177.8mm | 193.68mm | 7117N | 50.8mm |
| VIBSSM2B900 | 801660 | 101.6mm | 228.6mm | 203.2mm | 4004N | 50.8mm |

| Catalog Number | Article Number | Length | Width | Height | Ultimate Static Load | Deflection |
|----------------|----------------|---------|---------|---------|----------------------|------------|
| VIBSSM2B500 | 801656 | 101.6mm | 228.6mm | 203.2mm | 2224N | 50.8mm |

Table 3/3

| Catalog Number | Article Number | Length | Width | Height | Ultimate Static Load | Deflection |
|----------------|----------------|---------|---------|----------|----------------------|------------|
| VIBSSM2B800 | 801659 | 101.6mm | 228.6mm | 203.2mm | 3559N | 50.8mm |
| VIBSSM2B300 | 801654 | 101.6mm | 228.6mm | 203.2mm | 1335N | 50.8mm |
| VIBSSM2B100 | 801652 | 101.6mm | 228.6mm | 203.2mm | 445N | 50.8mm |
| VIBSSM2A100 | 801639 | 101.6mm | 177.8mm | 193.68mm | 445N | 50.8mm |
| VIBSSM2B200 | 801653 | 101.6mm | 228.6mm | 203.2mm | 890N | 50.8mm |
| VIBSSM2A700 | 801644 | 101.6mm | 177.8mm | 193.68mm | 3114N | 50.8mm |
| VIBSSM2B1000 | 801661 | 101.6mm | 228.6mm | 203.2mm | 4448N | 50.8mm |
| VIBSSM2B700 | 801658 | 101.6mm | 228.6mm | 203.2mm | 3114N | 50.8mm |
| VIBSSM2B600 | 801657 | 101.6mm | 228.6mm | 203.2mm | 2669N | 50.8mm |
| VIBSSM2A1200 | 801648 | 101.6mm | 177.8mm | 193.68mm | 5338N | 50.8mm |
| VIBSSM2A800 | 801645 | 101.6mm | 177.8mm | 193.68mm | 3559N | 50.8mm |
| VIBSSM2B1400 | 801663 | 101.6mm | 228.6mm | 203.2mm | 6228N | 50.8mm |
| VIBSSM2A1000 | 801647 | 101.6mm | 177.8mm | 193.68mm | 4448N | 50.8mm |
| VIBSSM2A040 | 801637 | 101.6mm | 177.8mm | 193.68mm | 178N | 50.8mm |
| VIBSSM2A900 | 801646 | 101.6mm | 177.8mm | 193.68mm | 4004N | 50.8mm |
| VIBSSM2A300 | 801641 | 101.6mm | 177.8mm | 193.68mm | 1335N | |
| VIBSSM2A400 | 801642 | 101.6mm | 177.8mm | 193.68mm | 1780N | |
| VIBSSM2A200 | 801640 | 101.6mm | 177.8mm | 193.68mm | 890N | |

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

