

Universal Structural Bracket, Strut Brace



CERTIFICATIONS



FEATURES

Used for installations where strut brace is perpendicular to structure

One wrench size fits all required hardware, eliminating the need to change tools

Shear-off head helps ensure correct torque and simplifies inspection

SPECIFICATIONS

Finish: Electrogalvanized

Material: Steel

Table 1/2

| Catalog Number | Article Number | Hole Size (HS) | Width (W) | Thickness (T) | A | B |
|----------------|----------------|----------------|-----------|---------------|----------|---------|
| CSBUS1 | 404568 | 14.3 mm | 40.6 mm | 6.4 mm | 133.4 mm | 12.7 mm |
| CSBUS2 | 404569 | 20.6 mm | 40.6 mm | 6.4 mm | 133.4 mm | 12.7 mm |

Table 2/2

| Catalog Number | Article Number | C | D | E |
|----------------|----------------|---------|---------|-------|
| CSBUS1 | 404568 | 40.6 mm | 50.8 mm | 66 mm |

| Catalog Number | Article Number | C | D | E |
|----------------|----------------|---------|---------|-------|
| CSBUS2 | 404569 | 40.6 mm | 50.8 mm | 66 mm |

ADDITIONAL PRODUCT DETAILS

Cut length for strut member is +/- 1" (25 mm) of measured length.

| FM Loads | | | | | |
|-------------|-----------------------|--|-----------|-----------|-----------|
| Part Number | Brace Member | Horizontal Capacity per Installation Angle from Vertical | | | |
| | | 30° - 44° | 45° - 59° | 60° - 74° | 75° - 90° |
| CSBUS1 | 41 x 41 Strut Channel | 8940 N | 12630 N | 15210 N | 16940 N |
| CSBUS2 | 41 x 41 Strut Channel | 8940 N | 12630 N | 15210 N | 16940 N |

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

