We connect and protect

ProLine Server Cabinet, 2000x600x1000mm, Lt Gray, Steel

Data Solutions

CATALOG NUMBER

PSC20610

The passively cooled ProLine Server Cabinet has a front viewing window and a wheeled base for application mobility and repositioning.

FEATURES

- Front window door with key lock and vents offers visibility and ventilation
- Open base with casters and levelers
- Fully perforated rear door promotes airflow providing passive cooling to equipment
- 2000-mm tall cabinets have split rear perforated doors
- Both front and rear doors provide security via lockable handles
- Quick-release latches on side panels provide easy service access
- Fully perforated top cover with two cable entry ports for easy access and service
- Mounting channels provide infinite front-to-back adjustment of rack angles

PRODUCT ATTRIBUTES

- Article Number: 38969
- Height: 2085mm
- Width: 608mm
- Depth: 999mm
- Material: Mild Steel

Finish: Powder Coated

Color: Light Gray

Color Code: RAL 7035

Thickness: 1.52mm

Rack Units: 42U

Additional Rack Angles: PRA1920THL1

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.