

# Rack-Mount Fan Speed Control

## Data Solutions



Perfect for offices, classrooms and other noise-sensitive areas, fan Speed Control optimizes airflow in a cabinet or rack, balancing air volume requirements with noise level and power use.

### INDUSTRY STANDARDS

UL 508 Listed; File No. E249700

cUL Listed per CSA C22.2 No. 14; File No. E249700

### FEATURES

Continuously variable fan speed control knob with minimum speed adjustment

Uses one RU rack space

Steel construction

Two NEMA 5-15R outlets provide power to fan

Six-foot (1.83-m) power cord plugs into standard 120 V 60 Hz outlet

### SPECIFICATIONS

Table 1/3

Catalog Number	Article Number	Height	Width	Depth	Max Current	Material
A19FANSC	14073	44mm	483mm	76mm	4A	Mild Steel

Table 2/3

Catalog Number	Article Number	Finish	Color	Color Code	Thickness	Temperature
A19FANSC	14073	Powder Coated	Jet Black	RAL 9005	2.66mm	45°C max

Table 3/3

Catalog Number	Article Number	Input Voltage AC
A19FANSC	14073	100 – 120V

## WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**