

Floor Stand Kit



The Floor Stand Kit easily installs on most Wall-Mount or Free-Stand enclosures for floor mounting or elevation. To install, drills holes in the bottom of the enclosure and bolt the floor stands to the enclosure. It is not necessary to remove the wall-mount brackets from the enclosure.

FEATURES

Each kit includes two stands

Two sets of floor stands are recommended for enclosures larger than double door Free-Stand enclosures

SPECIFICATIONS

Table 1/4

Catalog Number	Article Number	Material	Finish	Color	Color Code	Thickness
AFK0608SS6	27231	Stainless Steel 316L	Brushed			2.66mm
AFK1218SS6	27242	Stainless Steel 316L	Brushed			2.66mm
AFK0612SS6	27233	Stainless Steel 316L	Brushed			2.66mm
AFK0608SS	27208	Stainless Steel 304	Brushed			2.66mm
AFK1218SS	13453	Stainless Steel 304	Brushed			2.66mm
AFK1212SS6	27238	Stainless Steel 316L	Brushed			2.66mm
AFK1808SS6	27244	Stainless Steel 316L	Brushed			2.66mm
AFK1812SS6	27246	Stainless Steel 316L	Brushed			2.66mm
AFK1818SS6	27248	Stainless Steel 316L	Brushed			2.66mm
AFK1208SS6	27236	Stainless Steel 316L	Brushed			2.66mm
AFK0612SS	27214	Stainless Steel 304	Brushed			2.66mm
AFK0618	25730	Mild Steel	Powder Coated	Gray	ANSI 61	2.66mm
AFK2412SS	31360	Stainless Steel 304	Brushed			2.66mm
AFK2412SS6	27254	Stainless Steel 316L	Brushed			2.66mm
AFK1212SS	31330	Stainless Steel 304	Brushed			2.66mm
AFK1220	25650	Mild Steel	Powder Coated	Gray	ANSI 61	2.66mm
AFK2408SS	27225	Stainless Steel 304	Brushed			2.66mm
AFK2418SS6	27256	Stainless Steel 316L	Brushed			2.66mm
AFK1810SS6	27245	Stainless Steel 316L	Brushed			2.66mm
AFK1808SS	27217	Stainless Steel 304	Brushed			2.66mm

Table 2/4

Catalog Number	Article Number	Material	Finish	Color	Color Code	Thickness
----------------	----------------	----------	--------	-------	------------	-----------

AFK2410SS6	27253	Stainless Steel 316L	Brushed			2.66mm
AFK1210SS	31320	Stainless Steel 304	Brushed			2.66mm
AFK1208SS	31310	Stainless Steel 304	Brushed			2.66mm
AFK1818SS	27223	Stainless Steel 304	Brushed			2.66mm
AFK0624SS	27216	Stainless Steel 304	Brushed			2.66mm
AFK2412	25720	Mild Steel	Powder Coated	Gray	ANSI 61	2.66mm
AFK1212	25630	Mild Steel	Powder Coated	Gray	ANSI 61	2.66mm
AFK2424SS	27228	Stainless Steel 304	Brushed			2.66mm
AFK0612	25830	Mild Steel	Powder Coated	Gray	ANSI 61	2.66mm
AFK1824SS	27224	Stainless Steel 304	Brushed			2.66mm
AFK1224SS	13455	Stainless Steel 304	Brushed			2.66mm
AFK1810	25680	Mild Steel	Powder Coated	Gray	ANSI 61	2.66mm
AFK1812	25690	Mild Steel	Powder Coated	Gray	ANSI 61	2.66mm
AFK1816	25760	Mild Steel	Powder Coated	Gray	ANSI 61	2.66mm
AFK2416SS6	27255	Stainless Steel 316L	Brushed			2.66mm
AFK0610	25820	Mild Steel	Powder Coated	Gray	ANSI 61	2.66mm
AFK1218	25740	Mild Steel	Powder Coated	Gray	ANSI 61	2.66mm
AFK1216	25640	Mild Steel	Powder Coated	Gray	ANSI 61	2.66mm
AFK0618SS	27215	Stainless Steel 304	Brushed			2.66mm
AFK2410	25710	Mild Steel	Powder Coated	Gray	ANSI 61	2.66mm

Table 3/4

Catalog Number	Article Number	Material	Finish	Color	Color Code	Thickness
AFK2416	25780	Mild Steel	Powder Coated	Gray	ANSI 61	2.66mm
AFK0618SS6	27234	Stainless Steel 316L	Brushed			2.66mm
AFK1812SS	27221	Stainless Steel 304	Brushed			2.66mm
AFK2418SS	27227	Stainless Steel 304	Brushed			2.66mm
AFK1210	25620	Mild Steel	Powder Coated	Gray	ANSI 61	2.66mm
AFK2416SS	27226	Stainless Steel 304	Brushed			2.66mm

Catalog Number	Article Number	Material	Finish	Color	Color Code	Thickness
AFK0610SS	27213	Stainless Steel 304	Brushed			2.66mm
AFK2408	25700	Mild Steel	Powder Coated	Gray	ANSI 61	2.66mm
AFK1824SS6	27251	Stainless Steel 316L	Brushed			2.66mm
AFK0610SS6	27232	Stainless Steel 316L	Brushed			2.66mm
AFK1216SS	31340	Stainless Steel 304	Brushed			2.66mm
AFK0608	25810	Mild Steel	Powder Coated	Gray	ANSI 61	2.66mm
AFK1210SS6	27237	Stainless Steel 316L	Brushed			2.66mm
AFK1224SS6	27243	Stainless Steel 316L	Brushed			2.66mm
AFK1816SS	27222	Stainless Steel 304	Brushed			2.66mm
AFK1216SS6	27241	Stainless Steel 316L	Brushed			2.66mm
AFK1808	25670	Mild Steel	Powder Coated	Gray	ANSI 61	2.66mm
AFK2410SS	31350	Stainless Steel 304	Brushed			2.66mm
AFK1208	25610	Mild Steel	Powder Coated	Gray	ANSI 61	2.66mm
AFK1810SS	27218	Stainless Steel 304	Brushed			2.66mm

Table 4/4

Catalog Number	Article Number	Material	Finish	Color	Color Code	Thickness
AFK2424SS6	27257	Stainless Steel 316L	Brushed			2.66mm
AFK0624SS6	27235	Stainless Steel 316L	Brushed			2.66mm
AFK2408SS6	27252	Stainless Steel 316L	Brushed			2.66mm
AFK1816SS6	27247	Stainless Steel 316L	Brushed			2.66mm

ADDITIONAL PRODUCT DETAILS

Bulletin A80 applies to Mild Steel kits.

Bulletin A4SY applies to Stainless Steel kits.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE