

# Varistar CP Base/Plinth Side

Sides trim to mount to Varistar CP base/plinth



## FEATURES

Base/plinth sides, plain

## SPECIFICATIONS

**Product Type:** Cabinet/Rack Base

**Material:** Steel

Table 1/2

Catalog Number	Height	Depth	Package Quantity	Color	Color Code	Finish
24630-077	100mm	600mm	1	Black Grey	RAL 7021	Powder Coated
24630-083	100mm	300mm	1	Black Grey	RAL 7021	Powder Coated
24630-043	200mm	1200mm	1	Black Grey	RAL 7021	Powder Coated
24630-078	100mm	800mm	1	Black Grey	RAL 7021	Powder Coated
24630-040	100mm	1200mm	1	Black Grey	RAL 7021	Powder Coated
24630-080	200mm	600mm	1	Black Grey	RAL 7021	Powder Coated
24630-042	200mm	1100mm	1	Black Grey	RAL 7021	Powder Coated
24630-081	200mm	800mm	1	Black Grey	RAL 7021	Powder Coated
24630-038	100mm	1000mm	1	Black Grey	RAL 7021	Powder Coated
24630-079	100mm	900mm	1	Black Grey	RAL 7021	Powder Coated
24630-084	200mm	300mm	1	Black Grey	RAL 7021	Powder Coated
24630-039	100mm	1100mm	1	Black Grey	RAL 7021	Powder Coated
24630-082	200mm	900mm	1	Black Grey	RAL 7021	Powder Coated

Catalog Number	Height	Depth	Package Quantity	Color	Color Code	Finish
24630-041	200mm	1000mm	1	Black Grey	RAL 7021	Powder Coated

Table 2/2

Catalog Number	Type	Package Unit
24630-077	Plinth Side	Pair
24630-083	Plinth Side	
24630-043	Plinth Side	Pair
24630-078	Plinth Side	Pair
24630-040	Plinth Side	Pair
24630-080	Plinth Side	Pair
24630-042	Plinth Side	Pair
24630-081	Plinth Side	Pair
24630-038	Plinth Side	Pair
24630-079	Plinth Side	Pair
24630-084	Plinth Side	
24630-039	Plinth Side	Pair
24630-082	Plinth Side	Pair
24630-041	Plinth Side	Pair

## ADDITIONAL PRODUCT DETAILS

---

Please order base/plinth for front/rear separately.

Cannot be used in conjunction with castors

## WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Middle East & India

Dubai, United Arab  
Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**