


# VMEbus J2 Backplane

The nVent SCHROFF VMEbus Backplanes have outstanding high-frequency noise suppression and very high MTBF values due to ceramic capacitors and SMD fabrication technology.



## CERTIFICATIONS



## FEATURES

In accordance with ANSI/VITA 1-1994 VME64 standard

3 U with J2 plane

Connection or isolation between the digital GND and chassis GND can be changed via screw

Termination passive

Supply voltages can be provided via powerbugs (ring tag M4) or FASTONs

Multiple backplanes can be placed side by side without loss of slot space

## SPECIFICATIONS

Table 1/2

Catalog Number	Product Type	Number of Slots	Rack Height	Backplane Type	System Slot	Slot Width
23001-051	Backplane	21	3U	VMEbus, J2	Slot 1 Left	4HP
23001-046	Backplane	16	3U	VMEbus, J2	Slot 1 Left	4HP
23001-040	Backplane	10	3U	VMEbus, J2	Slot 1 Left	4HP
23001-036	Backplane	6	3U	VMEbus, J2	Slot 1 Left	4HP
23001-035	Backplane	5	3U	VMEbus, J2	Slot 1 Left	4HP

Catalog Number	Product Type	Number of Slots	Rack Height	Backplane Type	System Slot	Slot Width
23001-034	Backplane	4	3U	VMEbus, J2	Slot 1 Left	4HP
23001-033	Backplane	3	3U	VMEbus, J2	Slot 1 Left	4HP
23001-032	Backplane	2	3U	VMEbus, J2	Slot 1 Left	4HP

Table 2/2

Catalog Number	Connector Type	Power Connector Type	Height	Width	Package Quantity
23001-051	DIN 41612, C96	Power Bugs for M4 Cable Lugs	128.5mm	425.3mm	1
23001-046	DIN 41612, C96	Power Bugs for M4 Cable Lugs	128.5mm	321.3mm	1
23001-040	DIN 41612, C96	Power Bugs for M4 Cable Lugs	128.5mm	199.2mm	1
23001-036	DIN 41612, C96	Power Bugs for M4 Cable Lugs	128.5mm	120.5mm	1
23001-035	DIN 41612, C96	Power Bugs for M4 Cable Lugs	128.5mm	100.2mm	1
23001-034	DIN 41612, C96	Power Bugs for M4 Cable Lugs	128.5mm	79.8mm	1
23001-033	DIN 41612, C96	Power Bugs for M4 Cable Lugs	128.5mm	59.7mm	1
23001-032	DIN 41612, C96	Power Bugs for M4 Cable Lugs	128.5mm	40.4mm	1

## ADDITIONAL PRODUCT DETAILS

Other configurations available on request.

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

All locations

+1.763.422.2661

Chat with us:

[nvent.com/schroff](https://nvent.com/schroff)

### Europe

Straubenhardt, Germany

+49.7082.794.0

Betschdorf, France

+33.3.88.90.64.90

Warsaw, Poland

+48.22.209.98.35

Assago, Italy

+39.02.932.7141

Chat with us:

[nvent.com/schroff](https://nvent.com/schroff)

### Asia

Shanghai, China

+86.21.2412.6943

Qingdao, China

+86.532.8771.6101

Singapore

+65.6768.5800

Shin-Yokohama, Japan

+81.45.476.0271

Chat with us:

[nvent.com/schroff](https://nvent.com/schroff)

### Middle East & India

Dubai, United Arab

Emirates

+971.4.378.1700

Bangalore, India

+91.80.6715.2001

Istanbul, Turkey

+90.216.250.7374

Chat with us:

[nvent.com/schroff](https://nvent.com/schroff)



Our powerful portfolio of brands:

**CADDY**

**ERICO**

**HOFFMAN**

**ILSCO**

**SCHROFF**

**TRACHTE**