

Part Numbers for Lugs and Dies for Rail



Reduced lead times



Compatible
with nVent and Burndy tools



10 year warranty
when used with the complete
nVent ILSCO system



For over a century, nVent has been a leader in protecting critical railway systems and a champion for reliability. It's essential to continue this legacy of safety, which is why nVent is expanding its offering to include nVent ILSCO SureCrimp Lugs. This expansion ensures high-performance electrical connections are maintained for railway powered applications. With shorter lead times, and proven reliability, this refreshed offering delivers peace of mind and confidence to engineers and installers across North America.

NVENT ILSCO SURECRIMP CLNS PRODUCT FAMILY – LONG BARREL TYPE

CLNS-8-516	CLNS-1/0-38	CLNS-250-516	CLNS-500-38	CLNS-700-58
CLNS-6-516	CLNS-1/0-12	CLNS-250-38	CLNS-500-12	CLNS-750-12
CLNS-6-12	CLNS-2/0-516	CLNS-250-12	CLNS-500-58	CLNS-750-58
CLNS-4-516	CLNS-2/0-38	CLNS-250-58	CLNS-600-38	CLNS-1000-38
CLNS-4-38	CLNS-2/0-12	CLNS-300-516	CLNS-600-12	CLNS-1000-12
CLNS-2-516	CLNS-3/0-516	CLNS-300-38	CLNS-600-58	CLNS-1000-58
CLNS-2-38	CLNS-3/0-38	CLNS-300-12	CLNS-650-516	
CLNS-2-12	CLNS-3/0-12	CLNS-350-38	CLNS-650-38	
CLNS-1-38	CLNS-4/0-14	CLNS-350-12	CLNS-650-12	
CLNS-1-12	CLNS-4/0-516	CLNS-400-38	CLNS-650-58	
CLNS-1/0-14	CLNS-4/0-38	CLNS-400-12	CLNS-700-38	
CLNS-1/0-516	CLNS-4/0-12	CLNS-400-58	CLNS-700-12	



NVENT ILSCO SURECRIMP CLND PRODUCT FAMILY – LONG BARREL TYPE

CLND-8-12-134	CLND-3/0-58-134	CLND-400-58-134	CLND-1000-58-134
CLND-6-12-134	CLND-4/0-12-134	CLND-500-12-134	
CLND-4-12-134	CLND-4/0-58-134	CLND-500-58-134	
CLND-2-12-134	CLND-250-12-134	CLND-600-12-134	
CLND-1-12-134	CLND-250-58-134	CLND-600-58-134	
CLND-1/0-12-134	CLND-300-12-134	CLND-750-12-134	
CLND-2/0-12-134	CLND-300-58-134	CLND-750-58-134	
CLND-3/0-12-134	CLND-400-12-134	CLND-1000-12-134	



NVENT ILSCO SURECRIMP CSWS PRODUCT FAMILY – STANDARD BARREL TYPE

CSWS-8-8	CSWS-3-12	CSWS-3/0-14	CSWS-350-38	CSWS-650-12
CSWS-8-10	CSWS-2-14	CSWS-3/0-516	CSWS-350-12	CSWS-650-58
CSWS-8-14	CSWS-2-516	CSWS-3/0-38	CSWS-350-58	CSWS-700-38
CSWS-8-516	CSWS-2-38	CSWS-3/0-12	CSWS-350-34	CSWS-700-12
CSWS-8-38	CSWS-2-12	CSWS-3/0-58	CSWS-400-516	CSWS-700-58
CSWS-8-12	CSWS-1-10	CSWS-4/0-14	CSWS-400-38	CSWS-700-34
CSWS-6-10	CSWS-1-14	CSWS-4/0-516	CSWS-400-12	CSWS-750-12
CSWS-6-14	CSWS-1-516	CSWS-4/0-38	CSWS-400-58	CSWS-750-58
CSWS-6-516	CSWS-1-38	CSWS-4/0-12	CSWS-400-34	CSWS-750-34
CSWS-6-38	CSWS-1-12	CSWS-4/0-58	CSWS-500-516	CSWS-1000-38
CSWS-6-12	CSWS-1/0-14	CSWS-250-516	CSWS-500-38	CSWS-1000-12
CSWS-4-10	CSWS-1/0-516	CSWS-250-38	CSWS-500-12	CSWS-1000-58
CSWS-4-14	CSWS-1/0-38	CSWS-250-12	CSWS-500-58	CSWS-1000-34
CSWS-4-516	CSWS-1/0-12	CSWS-250-58	CSWS-500-34	
CSWS-4-38	CSWS-1/0-58	CSWS-300-516	CSWS-600-38	
CSWS-4-12	CSWS-2/0-14	CSWS-300-38	CSWS-600-12	
CSWS-3-10	CSWS-2/0-516	CSWS-300-12	CSWS-600-58	
CSWS-3-14	CSWS-2/0-38	CSWS-300-58	CSWS-600-34	
CSWS-3-516	CSWS-2/0-12	CSWS-350-14	CSWS-650-516	
CSWS-3-38	CSWS-2/0-58	CSWS-350-516	CSWS-650-38	



NVENT ILSCO U DIES PRODUCT FAMILY

U Dies Product Family	Description	U Dies Product Family	Description
ILD-21	U CMP DIE INDEX 21 RED	ILD-66	U CMP DIE INDEX 66 WHITE 300 KCMIL 250 FL
ILD-24-1	CMP DIE	ILD-71	U CMP DIE INDEX 71 RED 350 KCMIL 250 FLEX
ILD-29-1	U CMP DIE INDEX 29 GRAY	ILD-76	U CMP DIE INDEX 76 BLUE 400 KCMIL 300 FLE
ILD-33	U CMP DIE INDEX 33 BROWN 2 AWG	ILD-87	U CMP DIE INDEX 87 BROWN 500 KCMIL 350 F
ILD-37	U CMP DIE INDEX 37 GREEN 1 AWG 2 FLEX	ILD-94	U CMP DIE INDEX 94 GREEN 800 KCMIL 400 FL
ILD-42	U CMP DIE INDEX 42 PINK 1/0 AWG 1 FLEX	ILD-99	U CMP DIE INDEX 99 PINK 700 KCMIL 500 FL
ILD-45	U CMP DIE INDEX 45 BLACK 2/0 AWG 1/0 FLE	ILD-106	U CMP DIE INDEX #106 BLACK 750 KCMIL 600
ILD-50	U CMP DIE INDEX 50 ORANGE 3/0 AWG 2/0 FLE	ILD-125	U CMP DIE INDEX #125 WHITE 1000 KCMIL 750
ILD-54	U CMP DIE INDEX 54 PURPLE 4/0 AWG 3/0 FLE	ILD-KIT-CU	DIE KIT FOR CU SURECRIMP CONN15 DIES WIT
ILD-62	U CMP DIE INDEX 62 YELLOW 250 KCMIL 4/0 F		



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE