


Novastar Base/Plinth



Base Plate for Rear Cable Ducting which cut out for cable management. Opening is covered with plastic. Accessory brush strip can build in.

CERTIFICATIONS



FEATURES

Static load-carrying capacity 400 kg

Adjustable feet, height 57 mm ... 67 mm

St, 1.5 mm, RAL 7021

Cable ducting 110 x 76 mm

Incl. GND/earthing

SPECIFICATIONS

| | |
|----------------------|-------------------|
| Height: | 45mm |
| Product Type: | Cabinet/Rack Base |
| Material: | Steel |

Table 1/2

| Catalog Number | Width | Depth | Package Quantity | Color | Color Code | Finish |
|----------------|--------|--------|------------------|------------|------------|---------------|
| 27230-072 | 553mm | 800mm | 1 | Black Grey | RAL 7021 | Powder Coated |
| 27230-070 | 553mm | 500mm | 1 | Black Grey | RAL 7021 | Powder Coated |
| 27230-080 | 1000mm | 1000mm | 1 | Black Grey | RAL 7021 | Powder Coated |
| 27230-076 | 900mm | 900mm | 1 | Black Grey | RAL 7021 | Powder Coated |
| 27230-071 | 553mm | 600mm | 1 | Black Grey | RAL 7021 | Powder Coated |

Table 2/2

| Catalog Number | Type |
|----------------|-------------|
| 27230-072 | Base Plinth |
| 27230-070 | Base Plinth |
| 27230-080 | Base Plinth |
| 27230-076 | Base Plinth |
| 27230-071 | Base Plinth |

ADDITIONAL PRODUCT DETAILS

Please order brush strip separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations

+1.763.422.2661

Chat with us:

nvent.com/schroff

Europe

Straubenhardt, Germany

+49.7082.794.0

Betschdorf, France

+33.3.88.90.64.90

Warsaw, Poland

+48.22.209.98.35

Assago, Italy

+39.02.932.7141

Chat with us:

nvent.com/schroff

Asia

Shanghai, China

+86.21.2412.6943

Qingdao, China

+86.532.8771.6101

Singapore

+65.6768.5800

Shin-Yokohama, Japan

+81.45.476.0271

Chat with us:

nvent.com/schroff

Middle East & India

Dubai, United Arab

Emirates

+971.4.378.1700

Bangalore, India

+91.80.6715.2001

Istanbul, Turkey

+90.216.250.7374

Chat with us:

nvent.com/schroff



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE