

# CompacPRO Front Panel

The front panel for the CompacPRO Cases is bolted to the front frame of the case.



## CERTIFICATIONS



## FEATURES

The front panel is bolted to the front frame of the enclosure

## SPECIFICATIONS

|                        |             |
|------------------------|-------------|
| <b>Material:</b>       | Aluminum    |
| <b>Finish:</b>         | Anodized    |
| <b>Accessory Type:</b> | Front panel |
| <b>Product Type:</b>   | Front Panel |

Table 1/2

| Catalog Number | Rack Height | Rack Width | Depth | Package Quantity | Front Finish | Rear Finish |
|----------------|-------------|------------|-------|------------------|--------------|-------------|
| 30823-227      | 4U          | 63HP       | 3mm   | 1                | Anodized     | Anodized    |
| 30823-209      | 2U          | 42HP       | 3mm   | 1                | Anodized     | Anodized    |
| 30823-224      | 3U          | 63HP       | 3mm   | 1                | Anodized     | Anodized    |
| 30823-284      | 6U          | 84HP       | 3mm   | 1                | Anodized     | Anodized    |
| 30823-254      | 3U          | 28HP       | 3mm   | 1                | Anodized     | Anodized    |
| 30823-272      | 4U          | 84HP       | 3mm   | 1                | Anodized     | Anodized    |

| CatalogNumber | Rack Height | Rack Width | Depth | Package Quantity | Front Finish | Rear Finish |
|---------------|-------------|------------|-------|------------------|--------------|-------------|
| 30823-269     | 4U          | 42HP       | 3mm   | 1                | Anodized     | Anodized    |
| 30823-257     | 3U          | 42HP       | 3mm   | 1                | Anodized     | Anodized    |
| 30823-260     | 3U          | 84HP       | 3mm   | 1                | Anodized     | Anodized    |
| 30823-215     | 2U          | 84HP       | 3mm   | 1                | Anodized     | Anodized    |
| 30823-230     | 6U          | 63HP       | 3mm   | 1                | Anodized     | Anodized    |

| Table 2/2      |               |               |         |         |
|----------------|---------------|---------------|---------|---------|
| Catalog Number | Treated Edges | EMC Shielding | Height  | Width   |
| 30823-227      | No            | No            | 172.9mm | 345.4mm |
| 30823-209      | No            | No            | 84mm    | 238.7mm |
| 30823-224      | No            | No            | 128.4mm | 345.4mm |
| 30823-284      | No            | No            | 261.8mm | 452.1mm |
| 30823-254      | No            | No            | 128.4mm | 167.5mm |
| 30823-272      | No            | No            | 172.9mm | 452.1mm |
| 30823-269      | No            | No            | 172.9mm | 238.7mm |
| 30823-257      | No            | No            | 128.4mm | 238.7mm |
| 30823-260      | No            | No            | 128.4mm | 452.1mm |
| 30823-215      | No            | No            | 84mm    | 452.1mm |
| 30823-230      | No            | No            | 261.8mm | 345.4mm |

## ADDITIONAL PRODUCT DETAILS

Assembly Kit to fix one rear and one front panel is included with the case.

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**