Heavy Duty Pipe Clamp, Painted, Red Oxide, 355–363 mm OD, 14" Pipe

CATALOG NUMBER

SSG0359RO

FEATURES

- For high static requirements in industrial construction
- Suitable for fix point applications

PRODUCT ATTRIBUTES

- Article Number: 574725
- Material: Steel
- Finish: Painted;Red Oxide
- Outer Diameter (OD): 355 - 363 mm
- Pipe Size: 14"
- Hole Size (HS): 22 mm
- Screw Diameter (Sc): 20 mm
- Screw Length (L): 80mm
- Static Load: 2600N
- Width (W): 60 mm
- Thickness (T): 8 mm
- A: 427 mm

ADDITIONAL PRODUCT DETAILS

Static load refers to a complete set of Heavy Duty Pipe Clamps held in place with indicated screws per ISO 4014 and corresponding hex nuts per ISO 4032 (for further information, please refer to Standard SSG 7075E).

DIAGRAMS





WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America
+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical Support

Europe
Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe
Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC
Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

Our powerful portfolio of brands:
CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.