

Threaded Rod



FEATURES

Cut to length as needed

According to standard DIN 976-1 / ISO 7412

Property Class 4.8

SPECIFICATIONS

Table 1/2

Catalog Number	Article Number	E-Number	Material	Finish	Quality Class	Rod Size (RS)
050M61000S4	592700		Stainless Steel 304 (EN 1.4301)		70	M6
050M61000	592570	1522671	Steel	Electrogalvanized	4.8	M6
050M101000S4	592740		Stainless Steel 304 (EN 1.4301)		70	M10
050M121000	592630		Steel	Electrogalvanized	4.8	M12
050M161000	400332		Steel	Electrogalvanized	4.8	M16
050M101000HD	592615		Steel	Hot-Dip Galvanized	4.8	M10

Catalog Number	Article Number	E-Number	Material	Finish	Quality Class	Rod Size (RS)
050M81000S4	592720		Stainless Steel 304 (EN 1.4301)		70	M8
050M121000HD	592635		Steel	Hot-Dip Galvanized	4.8	M12
050M81000	592590	1522673	Steel	Electrogalvaniz ed	4.8	M8
050M121000S4	592760		Stainless Steel 304 (EN 1.4301)		70	M12
050M101000	592610	1522681	Steel	Electrogalvaniz ed	4.8	M10
050M122000	592640		Steel	Electrogalvaniz ed	4.8	M12
050M82000	592600	1522675	Steel	Electrogalvaniz ed	4.8	M8
050M103000	592670		Steel	Electrogalvaniz ed	4.8	M10
050M62000	592580		Steel	Electrogalvaniz ed	4.8	M6
050M63000	592650		Steel	Electrogalvaniz ed	4.8	M6
050M123000	592680		Steel	Electrogalvaniz ed	4.8	M12
050M102000	592620	1522698	Steel	Electrogalvaniz ed	4.8	M10
050M83000	592660	1522677	Steel	Electrogalvaniz ed	4.8	M8
050M82000S4	592730		Stainless Steel 304 (EN 1.4301)		70	M8

Table 2/2

Catalog Number	Article Number	E-Number	Material	Finish	Quality Class	Rod Size (RS)
050M62000S4	592710		Stainless Steel 304 (EN 1.4301)		70	M6
050M102000S4	592750		Stainless Steel 304 (EN 1.4301)		70	M10


Table 1/2

Catalog Number	Article Number	E-Number	Length (L)	Static Load
050M61000S4	592700		1000mm	2400N
050M61000	592570	1522671	1000mm	2400N
050M101000S4	592740		1000mm	7000N
050M121000	592630		1000mm	10000N
050M161000	400332		1000mm	18000N
050M101000HD	592615		1000mm	7000N
050M81000S4	592720		1000mm	4500N
050M121000HD	592635		1000mm	10000N
050M81000	592590	1522673	1000mm	4500N
050M121000S4	592760		1000mm	10000N
050M101000	592610	1522681	1000mm	7000N
050M122000	592640		2000mm	10000N
050M82000	592600	1522675	2000mm	4500N
050M103000	592670		3000mm	7000N
050M62000	592580		2000mm	2400N
050M63000	592650		3000mm	2400N
050M123000	592680		3000mm	10000N
050M102000	592620	1522698	2000mm	7000N
050M83000	592660	1522677	3000mm	4500N
050M82000S4	592730		2000mm	4500N

Table 2/2

Catalog Number	Article Number	E-Number	Length (L)	Static Load
050M62000S4	592710		2000mm	2400N
050M102000S4	592750		2000mm	7000N

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE

