

# Cable Entry Gland Plate Rectangular, CEPH



CEPH cable entry provides a very flat, space-saving professional cable entry with a very tight seal. The special shape of the membrane cone grommet helps ensure optimal strain relief.

## INDUSTRY STANDARDS

UL 508A Component Recognized; Type 1, 12, 4X (indoor only); File No. E61997

UL94 V-0 Flammability

NEMA Type 1, 12, 4X (indoor only)

CE

IP66

## FEATURES

Description: Fast, cost-effective cable entry with a tight seal for incoming cables and/or pneumatic conduits inside an enclosure. Can be affixed with screws or the built-in snap-in system that works for wall thicknesses of 1.5 to 2.5 mm.

Finish: Black

Flammability: UL94 V-0

Material: Polyamide 6.6 / TPE

Pack quantity: 1 pc

Protection: IP66, NEMA 1, 4x, 12 (Indoor use only)

Temperature resistance: -40°C to +90°C

## SPECIFICATIONS

Table 1/1

Catalog Number	E-Number	Cable Entry Quantity	Cable Entry	Cutout Size	Height	Width
CEPH2124	2506898	21	(1) 3.2 - 6.3 mm, (14) 4.0 - 7.5 mm, (4) 5.5 - 10.5 mm, (2) 8.0 - 12.5 mm	36 x 112mm	58mm	149.6mm
CEPH1624	2506896	16	(2) 3.2 - 6.3 mm, (9) 4.0 - 7.5 mm, (1) 5.5 - 10.5 mm, (1) 8.0 - 12.5 mm, (3) 12.0 - 16.2 mm	36 x 112mm	58mm	149.6mm
CEPH16124	2506895	16	(8) 3.2 - 5.5 mm, (6) 5.0 - 8.5 mm, (2) 9.5 - 14.5 mm	36 x 112mm	58mm	149.6mm
CEPH3224	2506899	32	(32) 3.2 - 6.3 mm	36 x 112mm	58mm	149.6mm
CEPH2024	2506897	20	(12) 3.2 - 6.3 mm, (8) 5.5 - 10.5 mm	36 x 112mm	58mm	149.6mm
CEPH1324	2506894	13	(10) 3.2 - 6.3 mm, (3) 16.0 - 20.5 mm	36 x 112mm	58mm	149.6mm

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**