

# MTSB Spring Toggle with Nut/Washer



## FEATURES

Washer, nut and toggle included

For fixing into hollow walls, hollow ceilings and suspended ceilings

## SPECIFICATIONS

Table 1/2						
Catalog Number	Article Number	Material	Finish	Rod Size (RS)	Length (L)	Drill Bit Diameter
MTSB4	584410	Steel	Electrogalvanized	4	90mm	14mm

Table 2/2		
Catalog Number	Article Number	Ultimate Static Load (F)
MTSB4	584410	1750N

## ADDITIONAL PRODUCT DETAILS

The Ultimate Static Load value does not take into account the load-bearing characteristics of the supporting material. The appropriate safety factor is to be added to this load rating.

Spring toggle requires a minimum clearance of 35 mm (1.38") to open when installed.

## DIAGRAMS

---



## WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

+1.800.753.9221  
Option 1 – Customer Care  
Option 2 – Technical  
Support

### Europe

Netherlands:  
+31 800-0200135  
France:  
+33 800 901 793

### Europe

Germany:  
800 1890272  
Other Countries:  
+31 13 5835404

### APAC

Shanghai:  
+ 86 21 2412 1618/19  
Sydney:  
+61 2 9751 8500



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**

