


# Varistar CP Steel Door, Perforated With 1-Point Locking, Key Plate Only, RAL 7021, 24 U, 1200H 800W

## Data Solutions

### CATALOG NUMBER

**21630-508**



Varistar CP Perforated Steel Door, IP 20 with Single Point Locking.

### FEATURES

Perforated steel door with single point locking for IP 20 protection class

Opening angle 180°

Key lock cover

### PRODUCT ATTRIBUTES

Rack Height: 24U

Height: 1200mm

Width: 800mm

Locking Type: Single Point Locking

Package Quantity: 1

Color: Black Grey

Color Code: RAL 7021

Complies With: IEC 61587-1

Material: Steel

Product Family: Varistar CP

Product Type: Cabinet Door

Protection Rating: IP20

Type: Steel Door, Perforated

Works With: Varistar CP

Net Weight: 11.252kg

## ADDITIONAL PRODUCT DETAILS

---

24U - 33U IP20 doors have 2 hinges, 38U - 52U IP20 doors have 3 hinges to ensure robust IP20 closing structures for taller cabinets

Please order lever handle 24630003 and the DIN lock separately if you want to replace the 1333 DIN lock lever handle

Please purchase the grounding kit separately.

## WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY**

**ERICO**

**HOFFMAN**

**ILSCO**

**SCHROFF**

**TRACHTE**