

## Depth interior profile, DIP



The DIP profile system is a 40 mm wide and 25 mm high profile, which can be mounted on the enclosure depth. It can also be used in combination with CLPF and CLPK profiles. Two rows of holes patterns for cage nut fixing and self-tapping screws are provided. DIP profiles are not compatible with adjustment in depth of the mounting plate.

### FEATURES

---

Description: The DIP profile system is a 40 mm wide and 25 mm high profile, which can be mounted on the enclosure depth. It can also be used in combination with CLPF and CLPK profiles. Two rows of holes patterns for cage nut fixing and self-tapping screws are provided. DIP profiles are not compatible with adjustment in depth of the mounting plate.

Material: Zinc plated steel.

Pack quantity: 4 profiles including fixing accessories.

## SPECIFICATIONS

---

**Thickness:** 1.5mm  
**Material:** Mild Steel  
**Finish:** Zinc Plated

Table 1/1

Catalog Number	Article Number	Height	Width	Depth	Load Rating	Enclosure Material
DIP210	DIP210	40mm	25mm	210mm	150N	Mild Steel
DIP300	DIP300	40mm	25mm	300mm	150N	Mild Steel
DIP400	DIP400	40mm	25mm	400mm	150N	Mild Steel
DIP260	DIP260	40mm	25mm	260mm	150N	Mild Steel

## WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**