

CS480 Straight Coupling



CS480 Straight Coupling attaches a tube to the enclosure, enabling 340-degree enclosure rotation. Maintenance-free bearings.

INDUSTRY STANDARDS

IEC 60529, IP66

FEATURES

Coupling can rotate 340 degrees with rotation stop

Torque preset at factory

Gasket and mounting hardware are included

Assembled CS480 HMI Arm System has a max weight load of 89.6 lb. (40.7 kg)

SPECIFICATIONS

Table 1/1

| Catalog Number | Article Number | Height | Width | Depth | Material | Finish |
|----------------|----------------|--------|-------|-------|---------------------|---------|
| CCSS48FC | 42459 | 60mm | 84mm | 84mm | Stainless Steel 304 | Brushed |

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE