

# Threaded Rod



## FEATURES

Cut to length as needed

According to standard DIN 976-1 / ISO 7412

Property Class 4.8

## SPECIFICATIONS


- Yield Strength:** 36000lbf/in<sup>2</sup>
- Tensile Strength:** 58000 lbf/in<sup>2</sup>
- Finish:** Electrogalvanized
- Material:** Steel

Table 1/1

Catalog Number	Rod Size (RS)	Length (L)	Static Load (F)
0502506EG	1/4"	6'	240lbf
0502510EG	1/4"	10'	240lbf
0503710EG	3/8"	10'	610lbf
0503706EG	3/8"	6'	600lbf
0505006EG	1/2"	6'	1130lbf
0505010EG	1/2"	10'	1130lbf
0506210EG	5/8"	10'	1810lbf
0506206EG	5/8"	6'	1810lbf
0507510EG	3/4"	10'	2710lbf
0507506EG	3/4"	6'	2710lbf

Catalog Number	Rod Size (RS)	Length (L)	Static Load (F)
0508706EG	7/8"	6'	3770lbf
0508710EG	7/8"	10'	3770lbf

## DIAGRAMS



## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

+1.800.753.9221  
Option 1 – Customer Care  
Option 2 – Technical  
Support

### Europe

Netherlands:  
+31 800-0200135  
France:  
+33 800 901 793

### Europe

Germany:  
800 1890272  
Other Countries:  
+31 13 5835404

### APAC

Shanghai:  
+ 86 21 2412 1618/19  
Sydney:  
+61 2 9751 8500



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**

