

# nVent CADDY Cat HP J-Hook Clip to Hammer-On Flange Clip, Swivel, 1/8"–1/4" Flange

## Data Solutions

### CATALOG NUMBER

---

**CATHP24**



### CERTIFICATIONS

---



### FEATURES

---

Requires only a hammer to install

Rotates 360 degrees to support various directional runs of cable

Requires no screws, rivets or special tools for assembly

J-Hooks feature bendable locking tabs that lock on to nVent CADDY Cat HP components to provide rigidity and stability

Link to J-Hooks in one of multiple color options to aid in pathway identification and organization

Customized J-Hook trees can be easily assembled with various J-Hook sizes, colors and configurations

nVent CADDY Cat HP components easily attach to any size nVent CADDY Cat HP J-Hook

### PRODUCT ATTRIBUTES

---

Material: Spring Steel


Finish: nVent CADDY Armour

Flange Thickness (FT): 0.125in

Static Load (F): 75lb

## DIAGRAMS

---



## WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**