

PDU, 0U, 30A(24A), 120V, 1P, 2 CB, (22)5-20R

Data Solutions

CATALOG NUMBER

EB0323

The Basic PDU is a cost-effective, reliable power distribution solution. Premium hydraulic-magnetic circuit breakers operate consistently in high-temperature environments. The Basic PDU offers advanced features, such as color-coded locking IEC outlets, a slim chassis design, and toolless mounting backed by a 5-year hassle-free warranty.

FEATURES

Black Powder Coated Chassis

IEC 62368 listed. RoHS, and REACH compliant. See drawing for additional information.

PRODUCT ATTRIBUTES

Product Family: Enlogic

Type: Basic PDU

Product Type: Socket Strip

Socket Type: (22) 5-20R

Socket Quantity: 22

Color: Black

Cable Length: 10ft

Switched Outlets: No

Circuit Breaker: 20 A, 1-pole, Hy-MagA

Power Rating: 2.9 kVA

Circuit Breaker Quantity: 2

Interrupt Rating: 5kAIC

Input Voltage: 120V

Phase: 1 PH

Nominal Power Output: 120VAC

Nominal Voltage: 120V

Number of Output Voltages: 22

Number of Phases: 1

On/Off Switch Included: No

Amperage (Derated Amperage): 30A (24A)

Output Voltage: 120VAC

Rack Units: 0U

Plug Type: NEMA L5-30P

Metering Type: None

Removable Input Cable: No

Material: Steel

Finish: Powder Coated

Height: 32.17in

Width: 2.05in

Depth: 2.09in

Weight: 7.92lb

Package Quantity: 1

ADDITIONAL PRODUCT DETAILS

Warranty : nVent Enlogic branded equipment provided shall be free from manufacturing defects for a period of five (5) years from the invoice date to the original purchaser.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE