

PDU, 0U, 30A(24A)NA/32A Int, 380-415V, 3P Wye, 6 CB, (24)C13 (24)4-in-1

Data Solutions

CATALOG NUMBER

EB0860



The Basic PDU is a cost-effective, reliable power distribution solution. Premium hydraulic-magnetic circuit breakers operate consistently in high-temperature environments. The Basic PDU offers advanced features, such as color-coded locking IEC outlets, a slim chassis design, and toolless mounting backed by a 5-year hassle-free warranty.

FEATURES

Black Powder Coated Chassis

IEC 62368 listed. RoHS, and REACH compliant. See drawing for additional information.

PRODUCT ATTRIBUTES

Product Family: Enlogic

Type: Basic PDU

Product Type: Socket Strip

Socket Type: (24) C13/C15; (24) C13/C15/C19/C21

Socket Quantity: 48

Color: Black

Cable Length: 10ft

Switched Outlets: No

Circuit Breaker: 20 A, 1-pole, Hy-MagA

Power Rating: 17.3 kVA North America; 22.1 kVA International

Circuit Breaker Quantity: 6

Nominal Power Output: 208VAC

Nominal Voltage: 415V

On/Off Switch Included: No

Amperage (Derated Amperage): 30 A (24 A) North America; 32 A International

Output Voltage: 208 – 230VAC

Rack Units: 0U

Plug Type: IEC 60309 530P6/532P6

Metering Type: None

Removable Input Cable: No

Material: Steel

Finish: Powder Coated

Height: 58.66in

Width: 2.2in

Depth: 2.17in

Package Quantity: 1

ADDITIONAL PRODUCT DETAILS

Warranty : nVent Enlogic branded equipment provided shall be free from manufacturing defects for a period of five (5) years from the invoice date to the original purchaser.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE