


MSP0 PDU, 2U, 60A(48A)NA/63A Int, 208V NA, 230V Int, 1P, 4 CB, (6)C13, (6)4-in-1

Data Solutions

CATALOG NUMBER

EN6354



The Advantage Series Outlet Metered, Outlet Switched PDU family offers energy metering with advanced power and environmental monitoring options and remote outlet on/off switching. Comprehensive monitoring at the input phase, circuit breaker, and individual outlet levels offers advanced alerts of potential overloads. Billing-grade metering provides accurate power consumption data for energy use optimization. The hot-swappable network management controller features Gigabit and redundant ethernet communication with advanced support for external environmental sensors and rack security access solutions.

PRODUCT ATTRIBUTES

Product Family: Enlogic

Product Type: Socket Strip

Socket Type: (6) C13/C15; (6) C13/C15/C19/C21

Circuit Breaker: 20 A

Color: Black

Circuit Breaker Quantity: 4

Switched Outlets: Yes

Power Rating: 11.5 kVA North America; 14.5 kVA International

Interrupt Rating: 5kAIC

Number of Poles: 1

Input Voltage: 208V

Phase: 1 PH

Output Voltage: 208 – 230VAC

Plug Type: IEC 60309 360P6 (IP44)

Nominal Voltage: 230V

Removable Input Cable: No

Amperage (Derated Amperage): 60 A (48 A) North America; 63 A International

Rack Units: 2U

Type: Intelligent PDU

Finish: Powder Coated

Metering Type: Outlet

Material: Steel

Height: 3.43in

Weight: 17.64lb

Width: 17.48in

Depth: 10.59in

Package Quantity: 1

ADDITIONAL PRODUCT DETAILS

87 mm L x 444 mm W x 269 mm D, (269 mm D at CB)

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE