

ProLine ConneCTek Communications Patch Cabinet

Data Solutions



The ProLine ConneCTek Network Communication/Patch Cabinets feature two vertical cable managers in the front of the cabinet and two rear cable managers for maximum cable routing and support. Cabinets are available in two widths to accommodate high-density cables, patch cords and networking equipment.

FEATURES

Aesthetically pleasing front door offers optimal airflow and durability

Fully perforated top, front door and rear doors allow maximum air movement around cables, patch panels and other network equipment

Front and rear open cable managers provide ability to support and route cable

Side-less models allow for easy installation in ganging applications

Common profiles allow ganging of server and networking cabinets

Top gland plate allows easy routing of cable, pre-terminated cables and patch panels

Three-point locking swing handle allows for easy but controlled access; two keys included

SPECIFICATIONS

- Color:** Jet Black
- Material:** Mild Steel
- Finish:** Powder Coated
- Color Code:** RAL 9005

Table 1/2

Catalog Number	Article Number	Height	Width	Depth	Thickness	Rack Units
----------------	----------------	--------	-------	-------	-----------	------------

PNC24810B	26393	94.92in	31.74in	39.33in	16ga	51U
PNC20711B	15615	78.37in	27.85in	43.28in	16ga	42U
PNC24811B	26394	94.92in	31.74in	43.27in	16ga	51U
PNC20811BNS	16073	78.37in	31.46in	43.28in	16ga	42U
PNC21812B	26391	85.08in	31.74in	47.2in	16ga	45U
PNC2089BNS	16071	78.37in	31.46in	35.4in	16ga	42U
PNC21811B	26388	85.08in	31.74in	43.27in	16ga	45U
PNC2079B	15613	78.37in	27.85in	35.4in	16ga	42U
PNC20711BNS	15621	78.37in	27.52in	43.28in	16ga	42U
PNC20710BNS	15618	78.37in	27.52in	39.34in	16ga	42U
PNC20811B	16067	78.37in	31.8in	43.28in	16ga	42U
PNC24812B	26395	94.92in	31.74in	47.2in	16ga	51U
PNC2089B	16065	78.37in	31.8in	34.4in	16ga	42U
PNC20812B	16068	78.37in	31.8in	47.22in	16ga	42U
PNC20810B	16066	78.37in	31.8in	39.34in	16ga	42U
PNC20812BNS	16074	78.37in	31.46in	47.22in	16ga	42U
PNC20712BNS	15622	78.37in	27.52in	47.22in	16ga	42U
PNC2079BNS	15617	78.37in	27.52in	35.4in	16ga	42U
PNC20710B	15614	78.37in	27.85in	39.34in	16ga	42U
PNC20810BNS	16072	78.37in	31.46in	39.34in	16ga	42U

Table 2/2

Catalog Number	Article Number	Height	Width	Depth	Thickness	Rack Units
PNC2189B	26386	85.08in	31.74in	35.39in	16ga	45U
PNC20712B	15616	78.37in	27.85in	47.22in	16ga	42U
PNC21810B	26387	85.08in	31.74in	39.33in	16ga	45U
PNC2489B	26392	94.92in	31.74in	35.39in	16ga	51U

Table 1/2

Catalog Number	Article Number	Side Covers Included
PNC24810B	26393	Yes
PNC20711B	15615	Yes
PNC24811B	26394	Yes
PNC20811BNS	16073	No

Catalog Number	Article Number	Side Covers Included
PNC21812B	26391	Yes
PNC2089BNS	16071	No
PNC21811B	26388	Yes
PNC2079B	15613	Yes
PNC20711BNS	15621	No
PNC20710BNS	15618	No
PNC20811B	16067	Yes
PNC24812B	26395	Yes
PNC2089B	16065	Yes
PNC20812B	16068	Yes
PNC20810B	16066	Yes
PNC20812BNS	16074	No
PNC20712BNS	15622	No
PNC2079BNS	15617	No
PNC20710B	15614	Yes
PNC20810BNS	16072	No

Table 2/2

Catalog Number	Article Number	Side Covers Included
PNC2189B	26386	Yes
PNC20712B	15616	Yes
PNC21810B	26387	Yes
PNC2489B	26392	Yes

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE