

# Varistar CP Server Cabinet

## Data Solutions



Welded steel frame for high static load requirements.  
Prepared for 19" integration of IT assets.

### FEATURES

Preconfigured, ready to use cabinet

Static load-carrying capacity up to 1600 kg, dynamic 1000 kg

Ingress protection class IP 20

Installation of different IT equipment possible

Integrated air panels for front to back cooling

Can be easily integrated into aisle containment system

### SPECIFICATIONS

- Product Type:** Rack
- Cladding Color Code:** RAL 7021
- Frame Material:** Steel

Table 1/2

Catalog Number	Rack Height	Cladding Material	Cladding Color	Type	Package Quantity	Dynamic Load
10630-020	47U	Steel	Black Grey	Standard	1	2200lbf

Catalog Number	Rack Height	Cladding Material	Cladding Color	Type	Package Quantity	Dynamic Load
10630-019	47U	Steel	Black Grey	Standard	1	2200lbf
10630-026	47U	Steel	Black Grey	Side-by-Side	1	2200lbf
10630-023	42U	Steel	Black Grey	Side-by-Side	1	2200lbf
10630-017	42U	Steel	Black Grey	Standard	1	2200lbf
10630-018	42U	Steel	Black Grey	Standard	1	2200lbf
10630-024	42U	Steel	Black Grey	Side-by-Side	1	2200lbf
10630-025	47U	Steel	Black Grey	Side-by-Side	1	2200lbf

Table 2/2

Catalog Number	Finish	Material
10630-020	Powder Coated	Steel
10630-019	Powder Coated	Steel
10630-026	Powder Coated	Steel
10630-023	Powder Coated	Steel
10630-017	Powder Coated	Steel
10630-018	Powder Coated	Steel
10630-024	Powder Coated	Steel
10630-025	Powder Coated	Steel

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**