

Bases



Vented bases are designed to be used with nVent HOFFMAN Impeller packages and include a stainless steel mesh to prevent the ingress of debris. The vented bases have a provision to easily install a standard furnace filter. If vented bases are used, a maximum airflow furnace filter is recommended. Filters are not provided. Solid bases are designed to be used with a closed-loop cooling solution.

FEATURES

Vented bases are designed to provide additional airflow to WeatherFlo outdoor enclosures

SPECIFICATIONS

Material:	Aluminum
Finish:	Powder Coated
Color Code:	RAL 9003
Color:	Signal White

Table 1/1

Catalog Number	Article Number	Thickness	Gland Plate Openings
WFHD3VB6830	21012	0.125in	4
WFHD3B3630	21006	0.125in	2
WFHD3VB3630	21013	0.125in	2
WFHD3B6830	21007	0.125in	4

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE