

Cable Entry Gland Plate Rectangular, CEPL



CEPL cable entries are ideally suited for applications in which an enclosure requires many incoming or outgoing cables, but there is limited installation space. CEPL entries can be installed quickly and easily without using tools.

INDUSTRY STANDARDS

UL 508A Component Recognized; Type 1, 12; File No. E61997

UL94 V-0 Flammability

NEMA Type 1, 12

CE

IP54

FEATURES

Finish: Gray

Pack quantity: 10

Description: Fast, cost-effective and tool-free cable entry for incoming cables and/or pneumatic conduits inside an enclosure. The snap-in system works for wall thicknesses of 1.5 to 2.5 mm.

Temperature resistance: -40°C to +90°C

Flammability: UL94 V-0

Protection: IP54, NEMA 1, 12

Material: TPE

SPECIFICATIONS

Table 1/1

Catalog Number	Article Number	Cable Entry Quantity	Cable Entry	Configuration	Cutout Size	Height
CEPL1924	58299	19	(12) 0.04 - 0.26 ", (7) 0.04 - 0.48 "		1.42 x 4.41in	1.73in
CEPL1724	58297	17	(5) 0.04 - 0.41 ", (12) 0.04 - 0.50 "		1.42 x 4.41in	1.73in
CEPL4824	58304	48	(48) 0.04 - 0.26 "		1.42 x 4.41in	1.73in
CEPL4224	58303	42	(12) 0.04 - 0.28 ", (17) 0.04 - 0.25 ", (12) 0.04 - 0.20 ", (1) 0.04 - 0.19 "		1.42 x 4.41in	1.73in
CEPL1424	58296	14	(14) 0.04 - 0.048 "	12 x 1.0-15.0mm (.04-.59)	1.42 x 4.41in	1.73in
CEPL1224	58295	12	(12) 0.04 - 0.59 "		1.42 x 4.41in	1.73in
CEPL5024	58305	50	(50) 0.04 - 0.26 "		1.42 x 4.41in	1.73in
CEPL2624	58302	26	(16) 0.04 - 0.26 ", (4) 0.04 - 0.28 ", (4) 0.04 - 0.63 ", (2) ASI-LTG		1.42 x 4.41in	1.73in
CEPL1824	58298	18	(4) 0.04 - 0.26 ", (5) 0.04 - 0.41 ", (5) 0.04 - 0.49 ", (4) 0.04 - 0.63 "		1.42 x 4.41in	1.73in

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE