

# ProLine G2 Solid Top

ProLine G2 Solid tops are used to close the top opening on an enclosure frame.



## FEATURES

---

Lifting eyes can be used to attach the solid top, in place of the included hardware

Seamless polyurethane gasket (UL component recognized) provides a water-tight, dust-tight seal against moisture and contaminants

Additional support provisions need to be made to support top mount air conditioners or other top mount accessories

Includes four M12 hex bolts for installation

Solid Tops are finished with paint over plated surfaces

## SPECIFICATIONS

**Thickness:** 16ga  
**Color:** Light Gray  
**Color Code:** RAL 7035

Table 1/2

Catalog Number	Article Number	Height	Width	Depth	Material	Finish
P2T128	32643	46.4in	29.9in	0.65in	Mild Steel	Powder Coated
P2T168	32647	62.2in	29.9in	0.65in	Mild Steel	Powder Coated
P2T66HF	32658	22.8in	22in	0.65in	Mild Steel	Galvanized, Powder Coated
P2T68	32663	22.8in	29.9in	0.65in	Mild Steel	Powder Coated
P2T106	32635	38.5in	22in	0.65in	Mild Steel	Powder Coated
P2T165	32645	62.2in	18.1in	0.65in	Mild Steel	Powder Coated
P2T86HF	32667	30.7in	22in	0.65in	Mild Steel	Galvanized, Powder Coated
P2T164	32644	62.2in	14.1in	0.65in	Mild Steel	Powder Coated
P2T810	32664	30.7in	37.8in	0.65in	Mild Steel	Powder Coated
P2T166	32646	62.2in	22in	0.65in	Mild Steel	Powder Coated
P2T126	32642	46.4in	22in	0.65in	Mild Steel	Powder Coated
P2T84	32665	30.7in	14.1in	0.65in	Mild Steel	Powder Coated
P2T106HF	32634	38.5in	22in	0.65in	Mild Steel	Galvanized, Powder Coated
P2T125	32638	46.4in	18.1in	0.65in	Mild Steel	Powder Coated
P2T85	32666	30.7in	18.1in	0.65in	Mild Steel	Powder Coated
P2T86	32668	30.7in	22in	0.65in	Mild Steel	Powder Coated
P2T124	32637	46.4in	14.1in	0.65in	Mild Steel	Powder Coated
P2T108	32636	38.5in	29.9in	0.65in	Mild Steel	Powder Coated
P2T185	32648	70in	18.1in	0.65in	Mild Steel	Powder Coated
P2T45	32654	14.9in	18.1in	0.65in	Mild Steel	Powder Coated

Table 2/2

Catalog Number	Article Number	Height	Width	Depth	Material	Finish
P2T88	32672	30.7in	29.9in	0.65in	Mild Steel	Powder Coated
P2T188	32653	70in	29.9in	0.65in	Mild Steel	Powder Coated
P2T65	32657	22.8in	18.1in	0.65in	Mild Steel	Powder Coated
P2T64	32656	22.8in	14.1in	0.65in	Mild Steel	Powder Coated
P2T186	32652	70in	22in	0.65in	Mild Steel	Powder Coated
P2T104	32632	38.5in	14.1in	0.65in	Mild Steel	Powder Coated

Catalog Number	Article Number	Height	Width	Depth	Material	Finish
P2T46	32655	14.9in	22in	0.65in	Mild Steel	Powder Coated
P2T105	32633	38.5in	18.1in	0.65in	Mild Steel	Powder Coated
P2T66	32662	22.8in	22in	0.65in	Mild Steel	Powder Coated

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**