

ProLine S1 Rack Angles



Rack angles are sold in pairs that are RU marked on all sides. One side is tapped 10-32 while the other side is square hole (.375 x .375 inch). Both sides are spaced per EIA universal standard. Rack angles may be assembled in either tapped or square-hole configuration. Rack angles and mounting brackets are formed from heavy gauge steel. All hardware and brackets are included for assembly into cabinet.

FEATURES

Rack angles are sold in pairs that are RU marked on all sides

One side is tapped 10-32 while the other side is square hole (.375 x .375 inch)

Both sides are spaced per EIA universal standard

Rack angles may be assembled in either tapped or square-hole configuration

Rack angles and mounting brackets are formed from heavy gauge steel

All hardware and brackets are included for assembly into cabinet

SPECIFICATIONS

Table 1/1

Catalog Number	Article Number	Height	Width	Depth	Material	Finish
PS1RA127	36756	47.24in	27.56in	27.56in	Mild Steel	Powder Coated
PS1RA217	36758	82.68in	27.56in	27.56in	Mild Steel	Powder Coated
PS1RA218	36914	82.68in	31.5in	31.5in	Mild Steel	Powder Coated
PS1RA237	39248	90.55in	27.56in	27.56in	Mild Steel	Powder Coated
PS1RA238	39251	90.55in	31.5in	31.5in	Mild Steel	Powder Coated
PS1RA236	39247	90.55in	23.62in	23.62in	Mild Steel	Powder Coated
PS1RA216	36757	82.68in	23.62in	23.62in	Mild Steel	Powder Coated
PS1RA126	36755	47.24in	23.62in	26.62in	Mild Steel	Powder Coated

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE