

ProLine Solid Door



Solid Doors include a removable door bar system on doors taller than 700 mm and wider than 400 mm. Hinge side is reversible. A flush bezel latch operates the 3-point latching system. Doors for 700-mm frames have 2-point latching. Hidden hinges (130-degree swing) permit attachment to the front or back of each enclosure frame. The use of a side-door adapter or a cable entry cabinet allows doors to be attached to the sides of the enclosure frame.

FEATURES

EMC doors are finished with paint over plated surfaces

Optional data pockets, door stops, grounding kits and 180-degree hinges are available

Hinges have easy slide retained hinge pins

Door gasket is foam-in-place urethane to provide a resilient, seamless seal

Two grounding studs are furnished. All mounting hardware is included

SPECIFICATIONS

Color: Light Gray

Color Code: RAL 7035

Table 1/2

Catalog Number	Article Number	Material	Thickness	Dimensions	Door Type
PDS206HF2	13579	Mild Steel	16ga	76.34 x 23.31in	EMC
PDS76R	94840	Mild Steel	16ga	25.16 x 23.31in	Steel
PDS165	35019	Mild Steel	16ga	60.59 x 19.69in	Steel
PDS146HF2	13489	Mild Steel	16ga	52.72 x 23.31in	EMC
PDS204	25429	Mild Steel	16ga	76.34 x 15.75in	Steel
PDS186HF2	13539	Mild Steel	16ga	68.46 x 23.31in	EMC
PDS207HF2	13589	Mild Steel	16ga	76.34 x 27.24in	EMC
PDS166	94880	Mild Steel	16ga	60.59 x 23.31in	Steel
PDS146	94860	Mild Steel	16ga	52.72 x 23.31in	Steel
PDS186	94910	Mild Steel	16ga	68.46 x 23.31in	Steel
PDS227HF2	13629	Mild Steel	16ga	84.21 x 27.24in	EMC
PDS205	35039	Mild Steel	16ga	76.34 x 19.69in	Steel
PDS207	94960	Mild Steel	16ga	76.34 x 27.24in	Steel
PDS225	35049	Mild Steel	16ga	84.21 x 19.69in	Steel
PDS185	35029	Mild Steel	16ga	68.46 x 19.69in	Steel
PDS227	95000	Mild Steel	16ga	84.21 x 27.24in	Steel
PDS206	94950	Mild Steel	16ga	76.34 x 23.31in	Steel
PDS184	29824	Mild Steel	16ga	68.46 x 15.43in	Steel
PDS226	94990	Mild Steel	16ga	84.21 x 23.31in	Steel
PDS126	29822	Mild Steel	16ga	44.84 x 23.31in	Steel

Table 2/2

Catalog Number	Article Number	Material	Thickness	Dimensions	Door Type
PDS188HF2	13559	Mild Steel	14ga	68.46 x 31.18in	EMC
PDS128	29823	Mild Steel	14ga	44.84 x 31.18in	Steel
PDS2010	94980	Mild Steel	14ga	76.34 x 39.06in	Steel
PDS148HF2	13499	Mild Steel	14ga	52.72 x 31.18in	EMC
PDS208	94970	Mild Steel	14ga	76.34 x 31.18in	Steel
PDS148	94870	Mild Steel	14ga	52.72 x 31.18in	Steel
PDS208HF2	13599	Mild Steel	14ga	76.34 x 31.18in	EMC
PDS228	95010	Mild Steel	14ga	84.21 x 31.18in	Steel
PDS2010HF2	13609	Mild Steel	14ga	76.34 x 39.06in	EMC
PDS1810HF2	13569	Mild Steel	14ga	68.46 x 39.06in	EMC

Catalog Number	Article Number	Material	Thickness	Dimensions	Door Type
PDS188	94930	Mild Steel	14ga	68.46 x 31.18in	Steel
PDS78R	94850	Mild Steel	14ga	25.16 x 31.18in	Steel
PDS1810	94940	Mild Steel	14ga	68.46 x 39.06in	Steel
PDS2210	95020	Mild Steel	14ga	84.21 x 39.06in	Steel
PDS78RHF2	13479	Mild Steel	14ga	25.16 x 31.18in	EMC
PDS168	94900	Mild Steel	14ga	60.59 x 31.18in	Steel

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE