

Rack-Mountable Fan Assemblies



Fan trays are a versatile solution to cooling card cages and racks. Redundant cooling with optional failure detection makes this air mover the obvious choice for sensitive equipment. Minimal rack space and repositionable fans are suited to today's smaller enclosures.

INDUSTRY STANDARDS

UL recognized

CSA Certified Motors

CE

FEATURES

Slim 1.75 inch (44 mm) Panel Height

19-inch rack mountable

Field adjustable fan strips to optimize air flow

Easy access to fan tray from front and back

Simplified installation without the need for side access

Support bracket

Exhaust Guard

6-inch Power Cord AC trays, Terminal block on DC trays

Permanently lubricated ball bearing motors

100% functionally tested

SPECIFICATIONS

Color: Light Gray
Material: Mild Steel
Finish: Powder Coated
Color Code: RAL 7035

Table 1/1						
Catalog Number	Article Number	Height	Width	Depth	Thickness	Fan Quantity
UEB17H230	22273	1.75in	19in	8in	16ga	3
UEB17H115	22267	1.75in	19in	8in	16ga	3

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE