

On Board Rack



Suitable for ongoing vibrations, shock, high temperatures, and high humidity.

CERTIFICATIONS



FEATURES

For mobile railway applications

Suitable for ongoing vibrations, shock, high temperatures, and high humidity

Suitable for 1, 2, or 3 U SNCF subracks (NF F61-005, CF 60-002)

Rear side is equipped for standard connectors; crossbar can be custom-coded for the SNCF coding pins

Crossbar with integrated cable channel

Several racks can be stacked or fitted in rows

Produced using a welding process, certified to EN 15085 (CL2)

Stainless Steel welds passivated to prevent corrosion

SPECIFICATIONS

| | |
|------------------------|--------------------------------|
| Static Load: | 25kg |
| Depth: | 341.8mm |
| Product Type: | Rack |
| Complies With: | SNCF NFF 61005; SNCF NFF 60002 |
| Frame Material: | Steel |

Table 1/1

| Catalog Number | Rack Height | Height | Rack Width | Width | Package Quantity | Material |
|----------------|-------------|---------|------------|----------|------------------|-----------------|
| 10170-013 | 6U | 290mm | 36HP | 252.65mm | 1 | Stainless Steel |
| 10170-017 | 9U | 423.4mm | 36HP | 252.65mm | 1 | Stainless Steel |
| 10170-012 | 6U | 290mm | 84HP | 496.4mm | 1 | Stainless Steel |
| 10170-014 | 3U | 156.7mm | 84HP | 496.4mm | 1 | Stainless Steel |
| 10170-016 | 9U | 423.4mm | 84HP | 496.4mm | 1 | Stainless Steel |
| 10170-015 | 3U | 156.7mm | 36HP | 252.65mm | 1 | Stainless Steel |

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE