

# Crimping Compression Tool, Foot Pump

## Data Solutions



### FEATURES

Wide cross section range

High-pressure 2 meter (6.5') long hose

Compact and easy to use

Includes easy-to-carry custom case

### SPECIFICATIONS

Table 1/1

Catalog Number	Article Number	Applied Force	System	Dies	Crimping Shape	Conductor Size
M4FP	716925	250kN	Foot pump hydraulic	PKM4 series	Hexagon	#6 Stranded - 1000 kcmil Stranded, 16 mm <sup>2</sup> Stranded - 625 mm <sup>2</sup> Stranded

### WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**