

# Extention Connector/Cable Assembly, for LED Light 1M

## Data Solutions

### CATALOG NUMBER

---

**57273**



The enclosure light provides a compact and flexible solution, and offers fast, easy assembly and installation. For mounting flexibility, the LED light can be fastened to the enclosure with screws or quickly attached to any flat steel surfaces with optional magnetic kits. A motion sensor is also available.

### CERTIFICATIONS

---



### FEATURES

---

Power cable for LED light mounting into cabinet

Lights can be easily mounted vertically or horizontally

Simple through-wiring based on a plug-and-play system

### PRODUCT ATTRIBUTES

---

Input Voltage AC: 250V max

Accessory Type: Lights

Protection Rating: IP20

Length: 1000mm

Package Quantity: 1

Color: Black

Finish: Smooth

Material: Plastic

Product Type: Light

Type: Connection Cable

Connection Type: Infeed; Trough-Wiring; 2-Pole

Nominal Voltage: 250V

Operating Temperature: 60°C min

Rated Current: 10A

Weight: 0.3kg

## WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**