

Dry Contact Cable

CATALOG NUMBER

EA9110



Dry Contact Cable to connect I/O sensors e.g. smoke for nVent SCHROFF RackPower PDU's.

FEATURES

Dry Contact Cable to connect I/O sensors e.g. smoke

1 m Cable to Sensor box with integrated magnet for easy mounting and 1.8 m connection Cable

For RackPower RP1xxx, RP2xxx, RP6xxx Series PDU's

Hot pluggable for easy integration

Operating Temperature range 0 to 65 °C

PRODUCT ATTRIBUTES

Product Type: Sensor

Works With: RackPower

Height: 260mm

Package Quantity: 1

Plug Type: RJ45

Product Family: Enlogic

Removable Input Cable: No

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations

+1.763.422.2661

Chat with us:

nvent.com/schroff

Europe

Straubenhardt, Germany

+49.7082.794.0

Betschdorf, France

+33.3.88.90.64.90

Warsaw, Poland

+48.22.209.98.35

Assago, Italy

+39.02.932.7141

Chat with us:

nvent.com/schroff

Asia

Shanghai, China

+86.21.2412.6943

Qingdao, China

+86.532.8771.6101

Singapore

+65.6768.5800

Shin-Yokohama, Japan

+81.45.476.0271

Chat with us:

nvent.com/schroff

Middle East & India

Dubai, United Arab

Emirates

+971.4.378.1700

Bangalore, India

+91.80.6715.2001

Istanbul, Turkey

+90.216.250.7374

Chat with us:

nvent.com/schroff



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE