


Wire Basket Tray PreForm Intersection



The nVent CADDY Wire Basket Tray PreForm Intersection is a precision-engineered solution designed to streamline cable tray installations at multi-pathway junctions. With its pre-galvanized steel base and interlocking polymer sidewalls, the PreForm Intersection delivers a clean, consistent, and tool-free installation experience.

Additionally, the PreForm Intersection significantly reduces installation time by eliminating the need for field cutting or job site configuration. This translates into improved productivity and increased efficiency, especially in retrofit scenarios where flexibility is critical.

CERTIFICATIONS



FONCTIONS

Multiple color options to coordinate with cable tray selection

Flame-retardant polymer rails ensure the safety of high-performance cabling

Routes cable systems in multiple directions

Provides a clean bend radius and helps to protect the natural bend radius of varying cable systems

SPÉCIFICATIONS

Finition: Prégalvanisé; Polyuréthane

Matériau: Acier

Table 1/2


Référence catalogue	Couleur	Hauteur (H)	Largeur (W)	Longueur (L)	Taille de trou (HS)	Rayon (R)
WBTI2X4		50.8 mm	511.48 mm	511.48mm		94.64mm
WBTI2X4BA	Noir	50.8 mm	511.48 mm	511.48mm		94.64mm
WBTI2X4WH	Blanc	50.8 mm	511.48 mm	511.48mm		94.64mm
WBTI2X6BA	Noir	50.8 mm	561.34 mm	561.34mm		94.64mm
WBTI2X6		50.8 mm	561.34 mm	561.34mm		94.64mm
WBTI2X20		50.8 mm	911.86 mm	911.86mm	19.05 mm	94.64mm
WBTI2X24WH	Blanc	50.8 mm	1016 mm	1016mm	19.05 mm	94.64mm
WBTI2X12WH	Blanc	50.8 mm	711.2 mm	711.2mm	19.05 mm	94.64mm
WBTI2X24BA	Noir	50.8 mm	1016 mm	1016mm	19.05 mm	94.64mm
WBTI2X12BA	Noir	50.8 mm	711.2 mm	711.2mm	19.05 mm	94.64mm
WBTI2X18BA	Noir	50.8 mm	861.06 mm	861.06mm	19.05 mm	94.64mm
WBTI2X24		50.8 mm	1016 mm	1016mm	19.05 mm	94.64mm
WBTI2X20BA	Noir	50.8 mm	911.86 mm	911.86mm	19.05 mm	94.64mm
WBTI2X18		50.8 mm	861.06 mm	861.06mm	19.05 mm	94.64mm
WBTI2X16BA	Noir	50.8 mm	812.8 mm	812.8mm	19.05 mm	94.64mm
WBTI2X12		50.8 mm	711.2 mm	711.2mm	19.05 mm	94.64mm
WBTI2X8WH	Blanc	50.8 mm	612.14 mm	612.14mm		94.64mm
WBTI2X8		50.8 mm	612.14 mm	612.14mm		94.64mm
WBTI2X8BA	Noir	50.8 mm	612.14 mm	612.14mm		94.64mm

Table 2/2

Référence catalogue	Poids unitaire	Certifications
WBTI2X4	0.907 kg	cUL, UL
WBTI2X4BA	0.907 kg	
WBTI2X4WH	0.907 kg	
WBTI2X6BA	1.361 kg	
WBTI2X6	1.361 kg	cUL, UL
WBTI2X20	6.35 kg	cUL, UL
WBTI2X24WH	8.165 kg	
WBTI2X12WH	3.175 kg	
WBTI2X24BA	8.165 kg	
WBTI2X12BA	3.175 kg	
WBTI2X18BA	5.443 kg	
WBTI2X24	8.165 kg	cUL, UL

Référence catalogue	Poids unitaire	Certifications
WBTI2X20BA	6.35 kg	
WBTI2X18	5.443 kg	cUL, UL
WBTI2X16BA	4.536 kg	
WBTI2X12	3.175 kg	UL, cUL
WBTI2X8WH	2.268 kg	
WBTI2X8	2.268 kg	cUL, UL
WBTI2X8BA	2.268 kg	

DIAGRAMMES



AVERTISSEMENT

Les produits nVent doivent être installés et utilisés uniquement comme indiqué dans les feuilles d'instructions et les documents de formation de nVent. Les feuilles d'instructions sont disponibles sur www.nvent.com et auprès de votre représentant du service client nVent. Une installation incorrecte, une mauvaise utilisation, une mauvaise application ou tout autre défaut de respect total des instructions et des avertissements de nVent peut entraîner une défaillance du produit, des dommages matériels, des blessures corporelles graves et la mort et/ou annuler votre garantie.

Amérique du Nord

+1 800 753 9221
Option 1 – Service client
Option 2 – Assistance
technique

Europe

Pays-Bas :
+31 800-0200135
France :
+33 800 901 793

Europe

Allemagne :
800 1890272
Autres pays :
+31 13 5835404

APAC

Shanghai :
+ 86 21 2412 1618/19
Sydney :
+61 2 9751 8500



Notre portefeuille puissant de marques:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

